









NOTE:

1:SPECIFICATION:



- 1.1 Voltage Rating: 60V AC/DC
- 1.2 Rated current : For signal pin 0.3 AMPS/Pin
For power pin 5 AMPS / Pin
- 1.3 Temperature Range: -40 °C to +85°C
- 1.4 Contact Resistance:
Signalpin:Initial:50mΩ MAX
AFTER TEST:Δ20mΩ
Power pin:Initial:15mΩ MAX
AFTER TEST:15mΩ MAX
- 1.5 Insulation Resistance
Initial: 1000 MΩ Minimum.
After test: 1000 MΩ Minimum.
- 1.6 Dielectric Withstanding Voltage
NO EVIDENCE OF BREAKDOWN IN AC 250 V,1 MINUTE
- 1.7 MATING-UNMATING FORCE:
MATING FORCE: 1 CYCLE: 50N MAX
30 CYCLE:50N MAX
UNMATING FORCE:1 CYCLE: 23.4N MIN
30 CYCLE:19.5N MIN
- 1.8 SALT WATER SPRAY: TEMPERATURE 35°C±2°C
DENSITY OF SALT WATER 5±1%
DURATION:48±2 HOUR
Storage Temperature Range -40°C to +85°C
0 to 90 % RH (Relative humidity).

3	POWER CONTACT	COPPER ALLOY, Au1u" Min ON CONTACT AREA, Au1u" Min ON SOLDER AREA, Ni 50u"Min ALL OVER	6	REEL	PLASTIC
2	SIGNAL CONTACT	COPPER ALLOY, Au1u" Min ON CONTACT AREA, Au1u" Min ON SOLDER AREA, Ni 50u"Min ALL OVER	5	COVER TAPE	PLLYESTER
1	HOUSING	LCP , BLACK, UL 94 V-0	4	EMBOSSED CARRIER TAPE	PS
NO.	PART NAME	DESCRIPTION , REMARKS	NO.	PART NAME	DESCRIPTION , REMARKS



深圳市华宇创精密电子有限公司


TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 0.3PH 单槽BTB 公座 78P	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW62M-BTB2X39-049B	
	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2511201639	
			SHEET NO. 1 OF 1	




STYLE AND DIMENSION OF REEL

PER REEL 15000 CONNECTORS

DIRECTION OF UNREELING



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2' X.X' ±0.5'  UNIT: mm [inch] SCALE:1:1 SIZE: A4		DRAWN BY :	DATE :	PART NAME:	
		陈一鸣	2014-02-23	包装图	
		CHECKED BY:	DATE :	PART NO.	
				MOLD NO.	
马跃	2014-02-23	DRAW NO:			
APPROVED BY:	DATE :	SHEET NO.	1 OF 1		
邱敏	2014-02-23				