



REV.	DESCRIPTION	DATE
A	首次发行	2025-11-28

### BNC SPECIFICATIONS

Electrical  
 Impedance 75 Ohms nominal  
 Frequency Range 0-12GHz (0-12 GHz on Extended Range Designs)  
 VSWR  
 12G Products: DC-6 GHz -20dB max.  
 12G Product: 6-12 GHz -15dB max.  
 Dielectric Withstanding Voltage 1500 VRMS  
 Voltage Rating 500 VRMS  
 Insulation Resistance 5000 MΩ min

Environmental  
 Temperature Range -65°C to +165°C  
 TPE Insulation -55°C to 85°C  
 Copolymer of Styrene -55°C to 85°C



PCB

序号	图号	图名	材料	质数	数量	备注
1	SY-B-174-1	本体	黄铜		1	镀镍
2	SY-B-173-2	针芯	磷青铜		1	镀金
3	SY-B-174-3	绝缘体	铁弗龙		1	白色
4	SY-B-174-4	绝缘体	铁弗龙		1	白色
5	SY-B-172-2	四方体	黄铜		1	镀镍



## 东莞市众驰电子有限公司

Dongguan Zhongchi Electronic Co., Ltd

Tel: 0769-81238620  
Fax: 0769-81238620

PART NAME: 12G SDI BNC FEMALE PCB		DATE: 2025-11-28	
PART NO.: ZC10.326105KE			
APPROVED BY	CHECKED BY	DESIGNED BY	
		HYH	
UNITS: mm		Tolerance	
SCALE: 1/1		X.X ±0.50	
REVISION: A		X.XX ±0.15	
		X.X° ±3°	