








NOTE:

1:SPECIFICATION:



- 1.1 Voltage Rating: 60V AC/DC
 - 1.2 Rated current : For signal pin 0.3 AMPS/Pin
For power pin 12 AMPS Max/(All Power Pin)
 - 1.3 Temperature Range: -40 °C to +85°C
 - 1.4 Contact Resistance:
Signalpin:Initial:50mΩ MAX
AFTER TEST:Δ20mΩ
Power pin:Initial:15mΩ MAX
AFTER TEST:15mΩ MAX
 - 1.5 Insulation Resistance
Initial: 500 MΩ Minimum.
After test: 500 MΩ Minimum.
 - 1.6 Dielectric Withstanding Voltage
NO EVIDENCE OF BREAKDOWN IN AC 100 V,1 MINUTE
 - 1.7 MATING-UNMATING FORCE:
MATING FORCE: 1 CYCLE: 40N MAX
30 CYCLE:40N MAX
UNMATING FORCE:1 CYCLE: 10N MIN
30 CYCLE: 8N MIN
 - 1.8 SALT WATER SPRAY: TEMPERATURE 35°C±2°C
DENSITY OF SALT WATER 5±1%
DURATION:48±2 HOUR
- Storage Temperature Range -40°C to +85°C
0 to 90 % RH (Relative humidity).

4	POWER CONTACT-B	COPPER ALLOY,AuAu* Min on CONTACT AREA,AuAu* Min on SOLDER AREA,Ni 50u*Min ALL OVER		
3	POWER CONTACT-A	COPPER ALLOY,AuAu* Min on CONTACT AREA,AuAu* Min on SOLDER AREA,Ni 50u*Min ALL OVER	7	REEL
2	SIGNAL CONTACT	COPPER ALLOY,AuAu* Min on CONTACT AREA,AuAu* Min on SOLDER AREA,Ni 50u*Min ALL OVER	6	COVER TAPE
1	HOUSING	LCP ,BLACK,UL 94 V-0	5	EMBOSSED CARRIER TAPE
NO.	PART NAME	DESCRIPTION , REMARKS	NO.	PART NAME
				DESCRIPTION , REMARKS



深圳市华宇创精密电子有限公司


TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 0.3PH 单槽BTB 母座68+6P	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW59F-BTB2X34-6-055B	
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2511201521	
			SHEET NO. 1 OF 1	



STYLE AND DIMENSION OF REEL

PER REEL 15000 CONNECTORS

DIRECTION OF UNREELING



深圳市华宇创精密电子有限公司

TOLERANCE:

X.X ± 0.30

X.XX ± 0.25

X.XXX ± 0.15

X.' ± 2 X.X' ± 0.5

UNIT: mm [inch]

SCALE:1:1 SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

包装图

CHECKED BY:

马跃

DATE :

2014-02-23

APPROVED BY:

邱敏

DATE :

2014-02-23

PART NO.

MOLD NO.

DRAW NO:

SHEET NO.

1 OF 1