

NOTES:

MATERIAL:

- 1.HOUSING MATERIAL :GLASS FILLED POLYESTER(UL94V-0).
- 2.CONTACT MATERIAL :PHOSPHOR BRONZE $\phi 0.46\text{mm}$ (C5100).
- 3.PLATING :GOLD PLATING OVER NICKEL.
- 4.SHIELD & COPPER ALLOY 0.20mm THICKNESS PLATING NI.

ELECTRICAL:

- 1.VOLTAGE RATING :125 VAC RMS.
- 2.CURRENT RATING :1.5 AMP.
- 3.CONTACT RESISTANCE :50 MILLIOHMS MAX.
- 4.INSULATION RESISTANCE :500 MEGOHMS MIN 500V DC.
- 5.DIELECTRIC WITHSTANDING MECHANICAL RESISTANCE :1000V AC RMS 50Hz. 1MIN.

- 1.DURRABILITY :750 CYCLES MIN.

- 2.PCB RETENTION PRE-SOLDER :1 LB MIN.

ENVIRONMENTAL:

2. OPERATION : -40°C TO $+85^{\circ}\text{C}$.

MATES WITH MODULAR PLUG CONFORMING TO

FCC PART 68,SUBPART F.

PART NUMBER: Δ

9812-0210810XX3X

9812 SERIES

PCB JACK

(9812系列PCB接口)

SHIELD (屏蔽壳):

- 1-W/O SHIELD (非屏)
- 2-HALF SHIELD (半包)
- 3-FULL SHIELD (全包)

PORTS (插口):

- 1-1X1 (一口) . 2-1X2 (二口)
- 4-1X4 (四口) . 5-1X5 (五口)
- 6-1X6 (六口) . 8-1X8 (八口)

POSITIONS (金针位置):

- 4-4POSITIONS (4P)
- 6-6POSITIONS (6P)
- 8-8POSITIONS (8P)
- 0-10POSITIONS (10P)

CONTACTS (金针根数):

- 2-2CONTACTS (2C) . 4-4CONTACTS (4C)
- 6-6CONTACTS (6C) . 8-8CONTACTS (8C)
- 0-10CONTACTS (10C)

PEG/TAB (边定位铁脚):

- 0-W/O PEG (无铁脚) . 1-FRONT PEG 3.05 (前脚3.05)
- 2-FRONT PEG3.68 (前脚3.68) . 3-FRONT PEG4.57 (前脚4.57)
- 4-BACK PEG3.05 (后脚3.05)

GOLD PLATING

(镀金厚度)

- 1-F 1U" . 2-1.5U"
- 3-3U" . 4-6U"
- 5-15U" . 6-30U"
- 7-50U"

LOGO (标识):

- 0-W/O LOGO (无标识) .
- 1-W/ HAXN (有HAXN标识)
- 2-W/ UL (有UL标识) .
- 3-W/ HAXN. UL (有HAXN. UL)

COLOR (颜色): 1-BLACK (黑色) .

2-WHITE (白色) . 3-GRAY (灰色)

4-IVORY (象牙色) . 5-YELLOW (黄色) .

6-RED (红色) . 7-GREEN (绿色)


PLASTIC (塑料):

1-PBT. 2-NYLON66 (尼龙66) .




3-NYLON46 (尼龙46) . 4-ABS

BACK PEG (后背铁脚):

- 0-W/O BACK PEG (无后背铁脚) .
- 1-1BACK PEG (1个后背铁脚)
- 2-2BACK PEG (2个后背铁脚) .
- 3-3BACK PEG (3个后背铁脚)



PEG/TAB



PC Board Layout

REVISION RECORD				
REV	ECO	DESCRIPTION	DRFT	CHKD
Δ		原始版本	PEILEI	05.10.08
Δ		更改尺寸	zushiyong	07.01.25

浙江创都电子科技有限公司		系列		名称	
RJ58-8CWL-BPB		98		A3	
不接比例		A3		B	
比例: 1:1		数量:		材料:	
表面处理:		批号:		日期:	
peilei		日期: 05.10.08		日期: 05.10.10	
GANBO		日期: 05.10.08		日期: 05.10.10	
zushiyong		日期: 05.10.10		日期: 05.10.10	
日期: 05.10.10		日期: 05.10.10		日期: 05.10.10	