


HSF



ROHS



PCB Layout Diagram
Top View

NOTE:

1. BASE: MAT'L: PBT BLACK
2. CONTACTS: Mn Steel, BRASS
3. ELECTRIC:
 - a. CONTACT RESISTANCE: 30 MILLIOHMS MAX
 - b. INSULATION RESISTANCE: 1000 MEGA OHMS MIN
 - c. DIELECTRIC VOLTAGE: 500V AC ONE SEC LEVEL
 - d. OPERATING TEMPERATURE: -25° C TO +85° C

Order code:

BT — S — SN — R — CR1620A
① ② ③ ④ ⑤

① BT: Coin Cell Holders

② Appearance for the product

M: SMT TYPE

S: 180 TYPE

R: 90 TYPE

③ Contact Plating

SN: Tin

G0: Gold flash

G1: 3U" Gold

G2: 5U" Gold

G3: 10U" Gold

G4: 15U" Gold

G5: 30U" Gold

④ Packing method

A: Tray packing

R: Tape & reel packing

⑤ Product number


CR1620A

Unless Otherwise specified tolerance
X. ± 0.35 X. XX: ± 0.20
X. X: ± 0.25 X. XXX: ± 0.15

SCALE: As Shown UNIT: mm

DRAW Jack Bao DATE 01/13/2019

CHECK BobYang DATE 01/13/2019



Antenk®

TITLE: Coin Cell Holders For CR1620

DRAWING NO: BT-S-SN-R-CR1620A

PRODUCT NO: BT-S-SN-R-CR1620A

△ Revise Dimensions

08/03/2022

REV

DESCRIPTION

DATE