

YASHIN POWER, Longhua District, Shenzhen,
Guangdong 518108, P. R. China
TEL: 17666139630

客户承认书

SPECIFICATION FOR APPROVAL

CUSTOMER/客户: _____

CUSTOMER P.N./客户物料号: _____

MODEL NO./产品型号: _____ **YSG-240-12N** _____

PRODUCT NO./产品编号: _____

SAMPLE DATE/送样日期: _____ **2024-09-24** _____

CUSTOMER AUTHORIZED SIGNATURE/客户承认签核		

Please return to us one copy of “SPECIFICATION FOR APPROVAL” with
you approved signature./客户确认签字，盖章后请回传一份承认书给我
司。

拟 制:	安规工程师:	项目工程师:	
龙建国 2024, 9. 24	蒋阳 2024, 9. 24	欧少年 2024, 9. 24	

**** Table Of Content/目录 ****

1. Functional description/功能描述.....	3
2. SCOPE/简述.....	3
2.1. Description/产品类型.....	3
3. Input Characteristics/输入特性	3
3.1. Input Voltage & Frequency/输入电压与频率	3
3.2. Input AC Current/AC 输入电流.....	3
3.3. Inrush Current (cold start)/浪涌电流(冷启动).....	4
3.4. Type Efficiency/典型效率.....	4
3.5. Energy Consumption /空载功耗	4
4. Output Characteristics/输出特性.....	4
4.1. Static Output Characteristics <Vo & R+N>/静态输出特性	4
4.2. Line/ Load Regulation/线性/负载调整率	4
4.3. Turn - on Delay Time/开机延迟时间	4
4.4. Hold-up Time/关机维持时间.....	4
4.5. Rise Time/上升时间.....	4
4.6. Fall Time/下降时间.....	4
4.7. Output Overshoot / Undershoot/输出过冲/欠冲.....	4
4.8. Output Load Transient Response/输出负载瞬态响应.....	5
5. Protection Requirements/保护要求.....	5
5.1. Over Current Protection/过流保护	5
5.2. Short Circuit Protection/短路保护	5
5.3. Over Voltage Protection/过压保护	5
5.4. Over temperature protection/过温保护	5
6. Environment Requirements/环境要求	5
6.1. Operating Temperature and Relative Humidity/操作温/湿度要求.....	5
6.2. Storage Temperature and Relative Humidity/存储温/湿度要求	5
6.3. Sea level shall be low 2.000 meters/低于 2000.	5
6.4. Vibration/振动	5
7. Reliability Requirements/可靠性要求	6
7.1. Burn-in/老化	6
7.2. E-caps lifetime	7
7.3. MTBF :	7
8. EMI/EMS Standards/EMI/EMS 标准	7
8.1. EMI Standards/EMI 标准	7
8.2. EMS Standards/EMS 标准	8
9. Safety Standards/安规标准	8
10. Mechanical Outline Drawing/外观示意图	9



1. Functional description/功能描述

YSG-240-12N 是一款 120W 或 240W /12V10A 和 24V10A 切换输出电源供应器,输入电压范围 180V~264Vac。采用铝外壳设计且具有很好的散热效果。该电源具有多种保护功能,如输入欠压保护、输出过流保护、输出过压保护、输出短路保护功能;符合 EN61000-3-2 谐波要求;为各种工程应用提供了一个高性能和高性价比的解决方案。

2. SCOPE/简述

The document detail the electrical, mechanical and environmental specifications of a SMPS, the power supply provide 240W continuous output power.

资料详细描述了一款 240W (连续输出功率)开关电源的电气性,结构性及环境等要求。

The power supply shall meet the **RoHS** requirement.

此款电源符合 RoHS 要求.

2.1. Description/产品类型

SMPS Adaptor(Wall mount)/插墙式适配器

Open Frame/开放式结构

Others/其他

SMPS Adaptor(Desk-top)/桌面型适配器

☒ SMPS Unit (With Case)/带铝壳型

3. Input Characteristics/输入特性

3.1. Input Voltage & Frequency/输入电压与频率

The range of input voltage is from 180Vac to 264Vac single phase, switching the input voltage through a switch.

输入电压范围: 从 180Vac 到 264Vac, 单相输入。

Items	Min/最小	Nom/额定值	Max/最大
Input Voltage/输入电压	180 Vac	200-240Vac	264Vac
Input Frequency/输入频率	47 Hz	50-60 Hz	63 Hz

3.2. Input AC Current/AC 输入电流

Input Voltage/输入电压	180Vac	264Vac	Full load
Input AC Current/AC 输入电流	3A Max	2.5A Max	Full load

3.3. Inrush Current (cold start)/浪涌电流(冷启动)

The energy of inrush current should not be over the I^2T of fuse & bridge diodes.
冷启动时, 浪涌能量不能超过整流桥和保险丝的 I^2T , 且不能有损坏。

3.4. Type Efficiency/典型效率

86% min.(average efficiency). @180Vac/50Hz input .12V Output

88% min.(average efficiency).@240Vac/60Hz input.24V Output

3.5. Energy Consumption /空载功耗

No load Consumption $\leq 0.8W$ (230Vac/50Hz).

在额定输入 230Vac/50Hz 时,空载功耗 $\leq 0.8W$ 。

4. Output Characteristics/输出特性

4.1. Static Output Characteristics <Vo & R+N>/静态输出特性

Output	Rated Load/额定负载		Output Range	R+N	Remark
Rate	Min. Load	Rate.Load	输出电压范围	纹波与噪声	备注
12V	0.0A	10A	11.4V ~ 12.6V	120mV	默认 (STB 断开)
24V	0.0A	10A	22.8V ~ 25.2V	240mV	STB 短路

Ripple & Noise: Measurement is done by 20MHz bandwidth oscilloscope and the output paralleled a 0.1uF ceramic capacitor and a 10uF electrolytic capacitor. (test under the condition of rated input and rated output).

纹波与噪声: 量测时示波器选用 **20MHz** 带宽限制, 输出端要并联一颗 **0.1uF** 的陶瓷电容和一颗 **10uF** 的电解电容. (在额定输入及输出的条件下检测)。

4.2. Line/ Load Regulation/线性/负载调整率

Output	Load Condition/负载条件		Line Regulation	Load Regulation	Remark
Rate	Min. Load	Rate.Load	线性调整率	负载调整率	备注
12V	0.0A	10A	± 5%	± 5%	默认 (STB 断开)
24V	0.0A	10A	± 5%	± 5%	STB 短路

4.3. Turn - on Delay Time/开机延迟时间

3S max. @180Vac to 240Vac input & Full load.

输入电压 **180Vac to 240Vac** 满载时, 开机延迟时间不超过 **3S**。

4.4. Hold-up Time/关机维持时间

10mS min. @ Full load & 230Vac/50Hz input turn off at worst case.

输入电压 **230Vac/60Hz** 满载时, 关机时间最差情况不小于 **10** 毫秒。

10mS min. @ Full load & 230Vac/50Hz input turn off at worst case.

输入电压 **230Vac/50Hz** 满载时, 关机时间最差情况不小于 **10** 毫秒。

4.5. Rise Time/上升时间

80 mS max. @ Full load & 180Vac/50Hz and 240Vac/50Hz input.

在 **180Vac/50Hz** 和 **240Vac/50Hz** 输入满载时, 上升时间不超过 **80** 毫秒。

4.6. Fall Time/下降时间

30 mS max. @ Full load.

满载时, 下降时间不超过 **30** 毫秒。

4.7. Output Overshoot / Undershoot/输出过冲/欠冲

10 % max. When the power on or off, when it is the full input voltage and full load.

开关机时, 输出过冲/欠冲均不大于 **10%**。

4.8. Output Load Transient Response/输出负载瞬态响应

输出电压 **12V** 或 **24V** 负载变化: 从 **25% to 50% to 25%**, **50% to 75% to 50%** 斜率: **0.25A/uS**, 动态响应恢复时间: **20mS**, 动态响应过冲 ± **10%**。

5. Protection Requirements/保护要求

5.1. Over Current Protection/过流保护

Over Power Point Limited: 110%~170% Full load

过流保护点限制: **110%~170%** 满载

The output shall hiccup when the over current applied to the output rail, and shall be self-recovery when the fault condition is removed.

当过流作用于输出时，输出将打嗝，当故障情况消除时，自动恢复。

5.2. Short Circuit Protection/短路保护

The input power shall decrease when the output short.the power supply shall no damage, and shall be auto-recovery when the fault condition is removed.

当输出短路时，输入功率应减小。电源不应损坏，故障排除后自动恢复。

5.3. Over Voltage Protection/过压保护

在 180~240Vac 输入时空载和满载情况下，输出过压保护且不能损坏。

6. Environment Requirements/环境要求

6.1. Operating Temperature and Relative Humidity/操作温/湿度要求

Operating temperature:-30℃ to +70℃

工作温度: -30℃ to +70℃

Operating Relative humidity:10%RH to 90%RH

工作湿度: 10%RH to 90%RH

6.2. Storage Temperature and Relative Humidity/存储温/湿度要求

Storage Temperature:-40℃ to +80℃

储存温度: -40℃ to +85℃

Storage relative humidity:10%RH to 95%RH non-condensing

存储湿度: 10%RH to 95%RH

6.3. Sea level shall be low 2.000 meters/低于 2000 米.

6.4. Vibration/振动

10 to 500Hz sweep at a constant acceleration of 2.0G(Displacement amplitude:

3.5mm),10 minutes per cycle, 60 minutes on the X, Y and Z axis.

以 2.0G 恒定加速度(位移幅值:3.5mm)扫频 10 - 500Hz, 每循环 10 分钟, X、Y、Z 轴 60 分钟。



7. Reliability Requirements/可靠性要求

7.1. Burn-in/老化

The power supply shall be burn-in for 2 Hours under rated input and 80% Full load at 40℃

±5℃.

电源在 40℃±5℃额定输入、80%满负荷情况下老化 2 小时。

7.2. E-caps lifetime

The E-caps used in this power supply must be with lifetime of 3 years @ 25℃of full load. @ 180-240Vac /50Hz.

本电源使用的电解电容寿命必须在 25℃满负荷时使用寿命为 3 年。@ 180-240Vac / 50Hz

7.3.MTBF :

≥200 K Hrs MIL-HDBK-217F (25℃).

平均无故障时间 20 万小时以上, 标准 MIL-HDBK-217F (25℃)。

8. EMI/EMS Standards/EMI/EMS 标准

8.1. EMI Standards/EMI 标准

EMI	Standards	Margin Measurements
-----	-----------	---------------------

Radiated Emission	EN55032 EN55035 GB/T9254 GB17625.1	≥3dB
Conduction Emission	EN55032 EN55035 GB/T9254 GB17625.1	≥3dB

8.2. EMS Standards/EMS 标准

8.2.1.EN 61000-4-2,electrostatic discharge(ESD) requirement/静电抗扰度要求

Discharge characteristic/静电规格	Test level/测试条件	Test criteria/测试标准
Air discharge/空气放电	+/- 8KV	A
Contact discharge/接触放电	+/- 4KV	A

8.2.2.EN 61000-4-3, radiated electromagnetic field susceptibility(rs)/辐射骚扰场强

Test level/测试条件	Test criteria/测试标准
10V/m (r.m.s)	A
30-1000MHz,80% AM(1KHz) sine-wave	

8.2.3.EN 61000-4-4,electric fast transients(burst) immunity requirement/电快速瞬变脉冲群

C oupling/测试端口	Test level/测试条件	Test criteria/测试标准
AC-input/交流输入	0.5KV	A
AC-input/交流输入	1KV	A

8.2.4.EN 61000-4-5,surge capability requirement/浪涌抗扰度要求

Surge voltage/雷击电压	Test criteria/测试标准
Common mode/共模 +/- 2KV	A
Differential mode/差模 +/-4KV	

8.2.5.EN 61000-4-6, Induced radio frequency fields conducted disturbances immunity requirement/电源端子传导骚扰实验

Test level/测试条件	Test criteria/测试标准
3V	A
0.15-30 MHz,80%AM(1KHz)	

8.2.6. Assessment criteria /评估标准

Acceptance criteria 可接受标准	Performance 性能
A	Agreed operational behavior within the specified limits 性能不允许变化；如果性能会发生变化，则变化的范围在产品规格书规定的范围内。
B	Time limited functional diminishment or malfunction during the tests is permitted. The function is self-reactivated by the unit following completion of the tests. 设备在测试过程中,性能降低允许在产品规格书要求范围内,干扰消除后,设备能恢复正常,不允许出现复位和任何方式的人工干预。
C	Malfunction is permitted .The function can be reactivated either by reconnection to the mains or by operator intervention. 在测试过程中，设备允许出现业务中断，测试完毕后允许自行恢复或者

人工干预恢复（包括硬件上干预）；测试中只允许初级防护器件损坏，并且更换损坏的初级防护器件后，设备能恢复正常

9. Safety Standards/安规标准

9.1. Dielectric Strength(Hi-pot)/介电耐压强度(高压)

I/P- O/P: 3KVac / 5mA max. / 60 second .

输入对输出: 3KVac / 5mA max. / 60 秒.

I/P-FG: 2KVac / 5 mA max. / 60 second .

输入对地: 2KVac / 5 mA max. / 60 秒

O/P-FG: 0.5K Vac / 5 mA max. / second.

输出对地: 0.5KVac / 5 mA max. / 60 秒.

9.2. Leakage Current/漏电流


3.5mA max. at 230Vac / 50Hz.

输入 230V AC,漏电流小于 3.5mA。

9.3. Insulation Resistance/绝缘阻抗

I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C/ 70% RH

输入对输出、输入对地、输出对地，在 25°C 70%的湿度分别施加 500Vdc 进行测试，阻抗大于 100 兆欧姆。



10. Mechanical Outline Drawing/外观示意图

199L*99W*50H mm

注：1.为保证安全，螺丝装入电源机壳长度 $L=3.5-4\text{mm}$

