

SOT-23 Fast Switching Diodes

Features

- Fast Switching Device (TRR <4nS)
- Power Dissipation of 225mW
- For General Purpose Switching Applications
- Dual Switching Diode

Applications

- Small signal switching
- Ultra high speed switching application

Mechanical Data




- Case: SOT-23
- Molding compound meets UL 94V-0 flammability rating, RoHS-compliant, halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750,Method 2026

Function Diagram

Reverse Voltage
100 V

Forward Current
0.15 Ampere

SOT-23







Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	VALUE
Reverse Breakdown voltage @I _R =100μA	V _{(BR)R}	V	100
Maximum Average Forward Rectified Current	I _{F(AV)}	mA	150
Non-Repetitive Peak forward surge current @t _p =1.0μs	I _{FSM}	A	2
Non-Repetitive Peak forward surge current @t _p =1.0s	I _{FSM}		1
Power Dissipation	P _d	mW	225
Storage temperature	T _{stg}	°C	-55 ~+150
Junction temperature	T _j	°C	-55 ~+150
Typical thermal resistance	R _{θJ-A}	°C /W	556

● Electrical Characteristics (Ta=25°C Unless otherwise noted)

PARAMETER	TEST CONDITIONS	SYMBOL	UNIT	Min	Type	Max
Maximum instantaneous forward voltage	$I_F=1.0\text{mA}$	V_F	V	0.55		0.7
	$I_F=10\text{mA}$			0.67	—	0.82
	$I_F=100\text{mA}$			0.75	—	1.10
	$I_F=150\text{mA}$			—	—	1.25
Reverse Leakage Current	$V_R=50\text{V}$	I_{R1}	μA	—	—	1
	$V_R=100\text{V}$	I_{R2}	μA	—	—	3
Total capacitance	$V_R=0\text{V}, f=1\text{MHz}$	C_T	pF	—	—	2
Maximum reverse recovery time	$I_F=10\text{mA}, I_{rr}=0.1\times I_{R2}, R_L=100\Omega$	T_{rr}	nS	—	—	4

● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)



● Ordering Information

PACKAGE	PACKAGE CODE	UNIT WEIGHT(g)	REEL(pcs)	BOX(pcs)	CARTON(pcs)	DELIVERY MODE
SOT-23	R1	0.008	3000	30000	180000	7"

● Package Outline Dimensions (SOT-23)

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	0.90	1.15	0.035	0.045
A1	-	0.10	-	0.004
A2	0.90	1.05	0.035	0.041
b	0.30	0.50	0.012	0.020
c	0.10	0.20	0.004	0.008
D	2.80	3.00	0.110	0.118
E	1.20	1.40	0.047	0.055
E1	2.25	2.55	0.089	0.100
e	0.950TYP		0.037TYP	
e1	1.80	2.00	0.071	0.079
L	0.550REF		0.022REF	
L1	0.30	0.50	0.012	0.020
θ	-	8°	-	8°

● Suggested Pad Layout

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
J	0.75	0.85	0.030	0.033
K	0.85	0.95	0.033	0.037
M	1.95	2.05	0.077	0.081
N	1.85	1.95	0.073	0.077