



HSF



ACTUAL SIZE



NOTE:

1. ALL INSIDE BEND RADII TO BE A MIN. OF MATERIAL THICKNESS UNLESS OTHERWISE SPECIFIED.
2. PART MUST BE FREE OF ALL BURRS AND SHARP EDGES.
3. MAT'L: 0.254 TH'K FULL HARD PHOSPHOR BRONZE
4. FINISH: NICKEL PLATE
0.00254-0.00762 NICKEL, OVER
0.00127-0.00254 COPPER
5. INDICATES CRITICAL DIMENSION

NOTES:

1. MATERIAL:
0.30mm PHOSPHOR BRONZE, NICKEL PLTD.
2. ROHS 2 COMPLIANT
Order code:

BS - M - SI - R - CR3002A
① ② ③ ④ ⑤

① BS: Battery Contacts

② Appearance for the product

M: SMT TYPE

③ Contact Plating

SI: Nickel Plate

SN: Tin

G0: Gold flash

G1: 3U" Gold

G2: 5U" Gold

G3: 10U" Gold

G4: 15U" Gold

G5: 30U" Gold

④ Packing:

B: Bag bulk packing


R: Tape & Reel packing

⑤ Product number

CR3002A

Unless Otherwise specified tolerance
X. ± 0.35 X. XX: ± 0.20
X. X: ± 0.25 X. XXX: ± 0.15

SCALE: As Shown UNIT: mm
DRAW: Lv Xun Hua DATE: 16/03/2019
CHECK: BobYang DATE: 16/03/2019



TITLE: BATTERY CONTACTS FOR CR3002, BR2016, DL2020,
CR2025, CR2032

DRAWING NO: BS-M-SI-R-CR3002A

PRODUCT NO: BS-M-SI-R-CR3002A

change BT-M-SN-3002-R to BS-M-SN-R-CR3002A

16/03/2019

REV



DESCRIPTION

DATE

HSF



RoHS



前后各空18个

- NOTES:
- TAPE AND REEL SPECIFICATIONS:
1. TAPE:
- MAT'L-ALL CONDUCTIVE POLYSTYRENE CARRIER
- ANSI/EIA-481 STANDARD
- 44.0 WIDE;24.0 PITCH
2. REEL:
- 330.2 DIA.500 PIECES OF
- PART NO.BS-M-SI-3002-R PER REEL.

Unless Otherwise specified tolerance

X. ±0.35 X.XX: ±0.20

X.X: ±0.25 X.XXX: ±0.15

SCALE:

As Shown

UNIT:

mm

DRAW

Lv Xun Hua

DATE


03/16/2019

CHECK

BobYang

DATE

03/16/2019



TITLE: BATTERY CONTACTS FOR CR3002. BR2016. DL2020. CR2025. CR2032

DRAWING NO: BS-M-SI-R-CR3002A

PRODUCT NO: BS-M-SI-R-CR3002A

change BT-M-SN-3002-R to BS-M-SN-R-CR3002A

16/03/2019

REV DESCRIPTION

DATE