

REVISION RECORD				
REV	ECO	DESCRIPTION	DRFT	CHKD

NOTES:

ELECTRICAL:

- VOLTAGE RATING :125 VAC RMS.
- CURRENT RATING :1.5 AMP.
- CONTACT RESISTANCE :30 MILLIOHMS MAX.
- INSULATION RESISTANCE :500 MEGOHMS MIN @ 500V DC .
- DIELECTRIC STRENGTH :1000V AC RMS 50Hz. 1MIN.

MECHANICAL:





- HOUSING MATERIAL :GLASS FILLED POLYESTER UL94V-0.
- CONTACT MATERIAL :PHOSPHOR BRONZE $\phi 0.46\text{mm}$.
- PLATING :GOLD PLATING OVER NICKEL.
- OPERATING :750 CYCLES MIN.
- SHIELDING :0.23mm THICKNESS COPPER ALLOY WITH NICKEL PLATED.
- PCB RETENTION PRE-SOLDER :1 LB MIN.

ENVIRONMENTAL:

- Temperature Range : $-45^{\circ}\text{C}\sim+85^{\circ}\text{C}$
- Relative Humidity : $90\sim95\%$ ($40\pm 2^{\circ}\text{C}$)

PART NUMBER:

DY 117 - ☐ ☐ ☐ 3u" ☐ 6u" ☐ 15u" ☐ 30u" ☐ 50u" ☐ PD20u"
☐ 10P8C ☐ 10P10C
Part No.



DETACHED LISTS	mm (inch)		DFTO:	DATE:	浙江创都电子科技有限公司			
			CHKD:	DATE:				
	Tolerance Exept as Noted		MFO:	DATE:				
	mm		APPVL:	DATE:	RJ58-10P10C			
	0±0.2	±						
	00±0.15	±						
	000±0.075	±						
	ANGLES ± 0.5		Q`TY:		DRAWING NO.		SIZE	REV
			FINISH:		/PART NO.		A4	06/06/02 0
			SCALE: 2:1		DO NOT SCALE DRAWING		SHEET	OF