

## FEATURES

- **Copper body** material for high conductivity and easy crimping
- **Tin plating** for resistance to corrosion
- **Added strength** and excellent conductivity
- **Vinyl insulation** for electrical insulation and terminal protection
- **Colour coded** insulation for easy identification of terminal size
- **Expanded insulation entry** for easy wire insertion

# RS PRO Insulated Ring Terminal, M6 Stud Size, 0.5mm<sup>2</sup> to 1.5mm<sup>2</sup> Wire Size, Red

RS Stock No.: 534-193



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

From RS PRO a high-quality insulated crimp ring terminal, also known as a ring connector or cable lug. Ring crimp terminals are used for connecting an electrical cable or wire to a stud or a post on an electrical component such as a battery terminal. This ring terminal is made from highly conductive copper and then tin plated for maximum electrical conductivity and corrosion resistance. A colour coded vinyl insulation provides protection to the terminal and aids quick identification of the terminal size. Once correctly crimped onto a wire or cable this ring terminal will provide a secure and reliable electrical connection

## General Specifications

<b>Insulation</b>	Insulated
<b>Insulation Material</b>	PVC
<b>Colour</b>	Red
<b>Contact Material</b>	Copper
<b>Contact Plating</b>	Tin
<b>Stud Size</b>	M6
<b>Application</b>	Wide range of industries for connecting wires to electrical components. Applications include wiring in industrial control systems and industrial machines, automotive applications, communication equipment, power supplies and domestic appliances.

## Mechanical Specifications

<b>Thickness</b>	0.8mm
<b>Overall Length</b>	26.7mm
<b>Inner Ring Diameter</b>	6.35mm
<b>Outer Ring Diameter</b>	11mm
<b>Maximum Wire Size</b>	1.5mm <sup>2</sup>
<b>Minimum Wire Size</b>	0.5mm <sup>2</sup>
<b>Maximum Wire Size (AWG)</b>	16AWG
<b>Minimum Wire Size (AWG)</b>	22AWG

## Operation Environment Specifications


Maximum Operating Temperature

150°C

## Approvals

Compliance/Certifications

2011/65/EU and 2015/863



Insulated		Wire range		Dimensions				Stud size	
Stock no.	AWG	mm <sup>2</sup>	Colour	B	D	L	I	AWG	mm
534238	22-16	0.5-1.5	Red	5.5	4.3	16.0	9.9	4	3.2
534222	22-16	0.5-1.5	Red	6.6	4.3	18.7	9.9	6	3.7
534216	22-16	0.5-1.5	Red	8.0	4.3	21.0	9.9	8	4.3
534200	22-16	0.5-1.5	Red	8.0	4.3	20.5	9.9	10	5.3
534193	22-16	0.5-1.5	Red	11.0	4.3	25.5	9.9	1/4	6.4
2082492	22-16	0.5-1.5	Red	12.0	4.3	27.0	9.5	5/16	8.4

Stock no.	AWG	mm <sup>2</sup>	Colour	B	D	L	I	AWG	mm
534597	16-14	1.5-2.5	Blue	6.7	4.8	19.0	9.9	6	3.7
534581	16-14	1.5-2.5	Blue	8.0	4.8	20.5	9.9	8	4.3
534575	16-14	1.5-2.5	Blue	9.5	4.8	22.0	9.9	10	5.3
534569	16-14	1.5-2.5	Blue	10.5	4.8	26.0	9.9	1/4	6.4
2082509	16-14	1.5-2.5	Blue	12.0	4.8	27.5	9.9	5/16	8.4

Stock no.	AWG	mm <sup>2</sup>	Colour	B	D	L	I	AWG	mm
534468	12-10	2.5-6.0	Yellow	7.2	6.5	27.0	13.5	6	3.7
534452	12-10	2.5-6.0	Yellow	9.5	6.5	26.5	13.5	8	4.3
534446	12-10	2.5-6.0	Yellow	9.5	6.5	27.0	13.5	10	5.3
534430	12-10	2.5-6.0	Yellow	11.0	6.5	29.0	13.5	1/4	6.4
534424	12-10	2.5-6.0	Yellow	14.0	6.5	34.0	13.5	5/16	8.4
2082537	12-10	2.5-6.0	Yellow	15.0	6.5	35.5	13.5	3/8	10.0