






Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 500V
Operation Temperature: -40 $^{\circ}$ to+105 $^{\circ}$
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240 $^{\circ}$ C for30-60seconds
(260 $^{\circ}$ C for 5 seconds)

P/N	PIN	DIM.A	DIM.B
XY-PM200-2-01P-Z-4.3	2*1	0.00	2.00
XY-PM200-2-02P-Z-4.3	2*2	2.00	4.00
XY-PM200-2-03P-Z-4.3	2*3	4.00	6.00
XY-PM200-2-04P-Z-4.3	2*4	6.00	8.00
XY-PM200-2-05P-Z-4.3	2*5	8.00	10.00
XY-PM200-2-06P-Z-4.3	2*6	10.00	12.00
XY-PM200-2-07P-Z-4.3	2*7	12.00	14.00
XY-PM200-2-08P-Z-4.3	2*8	14.00	16.00
XY-PM200-2-09P-Z-4.3	2*9	16.00	18.00
*****	*****	*****	*****
XY-PM200-2-40P-Z-4.3	2*40	(PIN-1)x2.0	(PIN)x2.0



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd				
TOLERANCE UNLESS OTHERWISE SPECIFIED						
.X±0.3	X.*± 5°	APR. Alex	TITLE: 2.0FH H4.3 2xnPin 180度 W4.5 U型 PC2.8 6T			
.XX±0.2	.X*± 1	CHK. Jack	DWG NO. XY-PM200-2-NP-Z-4.3			
.XXX±0.1	.XX*± 0.5	DRA. Can	PROJ. 		CUSTOMER DRAWING	
			SIZE A4	SCALE 1:1	SHEET 1/1	REV. A