

FEATURES

- Nylon 66 black body
- Solder lug / Spade terminals 6.3
- Easy to terminate, no special tools are required
- UL 94 V0 rated

RS PRO C14 Panel Mount IEC Connector Male, 10.0A, 250.0V

RS Stock No.: 488-191



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From the trusted RS PRO brand, a range of C14 appliance inlet connectors designed for panel mounting. The IEC chassis plugs feature industry standard 6.3 mm (1/4 inch) Faston terminals enabling rapid termination, no specialist tooling is required. Once the desired cut-out is made, these IEC C14 connectors simply snap-in to the panel and are securely retained by top and bottom spring-loaded tabs. Constructed from durable black Nylon 66 material, the RS PRO IEC C14 connectors are extremely robust and hardwearing. These RS PRO series of IEC inlet connectors are ideal for new designs, maintenance and repair.

General Specifications

IEC Connector Type	C14
Gender	Male
Body Orientation	Straight
Illuminated Switch	No
Shuttered	No
Body Material	Nylon-66
Colour	Black
Applications	Desktop computers, Monitors, Older Laptop power supplies, Printers, Audio and Video equipment, Test equipment, Power supplies, Commercial appliances

Electrical Specifications

Current Rating	10A
Voltage Rating	250VAC
Termination Method	Solder, Spade
Withstanding Voltage	2000VAC for 1 min
Insulation Resistance	>103MΩ
Contact Resistance	<10mΩ

Mechanical Specifications

Mounting Type	Panel Mount
Panel Thickness	2mm

Approvals

Compliance/Certifications	UL, CSA , TUV
----------------------------------	---------------



Dimensions



