


REV.	Q'TY	ECN. NO.	APR.	DATE

A  
B  
C  
D  
E  
F




A  
B  
C  
D  
E  
F



**SPECIFICATIONS**

Current Rating: 1.5 Amps  
 Insulation Resistance: 1000M $\Omega$  Min  
 Contact Resistance: 20m $\Omega$  Max  
 Withstanding Voltage: AC 500V  
 Operation Temperature: -40 $^{\circ}$ to+105 $^{\circ}$   
 Contact Material: Brass  
 Standard: PA6T  
 Insulator Material: Polyester(UL 94V-0)  
 Contact Plating: Gold Flash  
 Max.Processing Temp: 240 $^{\circ}$ C for30-60seconds  
 (260 $^{\circ}$ C for 5 seconds)

P/N	PIN	DIM.A	DIM.B
XY-PM200-2-01P-S-4.3	2*1	0.00	2.00
XY-PM200-2-02P-S-4.3	2*2	2.00	4.00
XY-PM200-2-03P-S-4.3	2*3	4.00	6.00
XY-PM200-2-04P-S-4.3	2*4	6.00	8.00
XY-PM200-2-05P-S-4.3	2*5	8.00	10.00
XY-PM200-2-06P-S-4.3	2*6	10.00	12.00
XY-PM200-2-07P-S-4.3	2*7	12.00	14.00
XY-PM200-2-08P-S-4.3	2*8	14.00	16.00
XY-PM200-2-09P-S-4.3	2*9	16.00	18.00
.....	.....	.....	.....
XY-PM200-2-40P-S-4.3	2*40	(PIN-1)x2.0	(PIN)x2.0



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 2.0FH H4.3 2xnPin SMT# W4.5 U# PC6.5 PB4.6 6T	
.X $\pm$ 0.3	X.* $\pm$ 5'	CHK.	Jack	DWG NO. XY-PM200-2-NP-S-4.3	
.XX $\pm$ 0.2	.X* $\pm$ 1	DRA.	Can	PROJ.  CUSTOMER DRAWING	
.XXX $\pm$ 0.1	.XX* $\pm$ 0.5	SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A