





REV.	Q'TY	ECN. NO.	APR.	DATE

**SPECIFICATIONS**

Current Rating: 3Amps  
 Insulation Resistance: 1000MΩ Min  
 Contact Resistance: 20mΩ Max  
 Withstanding Voltage: AC 1000V  
 Operation Temperature: -40°to+105°  
 Contact Material: Brass  
 Standard: PA6T  
 Insulator Material: Polyester(UL 94V-0)  
 Contact Plating: Gold Flash  
 Max.Processing Temp: 240°C for30-60seconds  
 (260°C for5seconds)

P/N	PIN	DIM.A	DIM.B
XY-PM254-2-01P-S-8.5	2*1	0.00	2.54
XY-PM254-2-02P-S-8.5	2*2	2.54	5.08
XY-PM254-2-03P-S-8.5	2*3	5.08	7.62
XY-PM254-2-04P-S-8.5	2*4	7.62	10.16
XY-PM254-2-05P-S-8.5	2*5	10.16	12.70
XY-PM254-2-06P-S-8.5	2*6	12.70	15.24
XY-PM254-2-07P-S-8.5	2*7	15.24	17.78
XY-PM254-2-08P-S-8.5	2*8	17.78	20.32
XY-PM254-2-09P-S-8.5	2*9	20.32	22.86
.....	.....	.....	.....
XY-PM254-2-40P-S-8.5	2*40	(PIN-1)X2.54	(PIN)X2.54



RECOMMEND P.C.B LAYOUT  
 PCB TOLERANCE:±0.05 (TOP VIEW)

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyecomm Electronics Co.,Ltd		
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 2.0FH H6.35 2xnPi2.54FH H8.5 2xnPin SMT U型 PC7.2 PBB.8 6Tn 180μ Y# PC2.8 6T
.X±0.3	X.*± 5°	CHK.	Jack	DWG NO. XY-PM254-2-NP-S-8.5
.XX±0.2	.X*± 1	DRA.	Can	PROJ.  CUSTOMER DRAWING
.XXX±0.1	.XX*± 0.5	SIZE	A4	SCALE 1:1 SHEET 1/1 REV. A