




REV.	ECN NO.	LOCAS.	DESCRIPTION	DATE	DESIGN
A0			图面发行	2013.06.13	Xingyue

NOTE:UNLESS OTHERWISE SPECIFIED

- 1.DIMENSION SHALL BE INTERPRETED PER ANSI Y14.5M-1994.
- 2.DIMENSION MARKED WITH" "SHOULD SPECIFIED ON INSPECTION PLAN
- 3.CONTACT PETENTION FORCE:0.2 N MIN
- 4.CONTACT MATERIAL:COPPER ALLOY
- 5.INSULATOR:HIGH TEMPERATURE PLASTIC UL94 V-0
- 6.LOW PROFILE:1.5MM MAX.MATING HEIGHT
- 7.APPLICATION FREQUENCY UP TO 6GHz



SECTION A-A'



RECOMMENDED PCB LAYOUT(TOP VIEW)

GENERAL TOLERANCES:±0.05

3	SHELL	COPPER ALLOY	Ni: 50u"~100u"/ Gold Flash.	1
2	CONTACT	COPPER ALLOY	Ni: 50u"~100u"/ Au: 5u" Min.	1
1	HOUSING	LCP(BLACK)	UL94V-0	1
ITEM	DESCRIPTION	MATERIAL	FINISH	Q'TY

COPLIANCE WITH THE REQUIEMENT ☐ RoHS ☐ HF ☐ SONY00259 ☐ OTHER
* NO USING RESTRICTED AND BANNED SUBSTANCE

DIM	TOL	DIM	TOL
X.	±0.20	X'	±4.0'
X.X	±0.15	X.X'	±3.0'
X.XX	±0.10		±2.0'
X.XXX	±0.05		±1.0'

DRAW NO.		DATE	DRAW NAME:	0.81换揖姚 础畝
DESIGN:	Xingyue	2013.06.13	FILE:	P/N NO. P1163-0250R
CHECK:			MODEL:	UNIT: mm SHEET: N/A
APPROVED:			REV. A0 SCALE N/A	