



### **Active ceramic antenna**

Model:

**BWGPSCNX8-8B1** 

Description:

GPS active ceramic antenna

Characteristics:

Frequency range: 1575 ± 5 MHz IPEX-1 inner hole connector

Structure: right-hand circularly polarized antenna

Cable type: RG1.13 Cable length: 120 mm.

Dimensions: 8 mm × 8 mm × 6.5 mm

Complies with RoHS and REACH regulations

www.batwireless.com



# **Contents**

1. Product description	3
2. Product specifications	4
3. Physical diagram	5
4. Dimensional drawing	6
5. Test equipment	7-8
6. Performance data	9-10
6.1 Voltage standing wave ratio	9
6.2 Return loss	9
6.3 Gain	10
6.4 Efficiency	10
6.5 Antenna gain and efficiency	10
7. Radiation pattern diagram	11-12
7.1 2D radiation pattern diagram	11
7.2 3D radiation pattern diagram	12

#### Legal statement:

In order to provide better service to users, Shenzhen Bat Wireless Technology Co., Ltd. (hereinafter referred to as "Bat Wireless") has endeavored to present detailed and accurate product information in this manual. However, since the contents of this manual are subject to time sensitivity, Bat Wireless cannot fully guarantee the timeliness and applicability of this document at all times. Bat Wireless reserves the right to update the contents of this manual without prior notice. To obtain the latest version of the information, esteemed users are advised to visit the official Bat Wireless website regularly or contact Bat Wireless staff. Thank you for your understanding and support!

Copyright Statement: All contents of this product manual (including text, charts, logos, and designs) are protected by copyright law and international copyright treaties. No organization or individual may reproduce, modify, distribute, transmit, or use any part or all of this manual in any form (including electronic, mechanical, or photocopying methods) without prior written authorization from our company. Infringers will bear corresponding legal liabilities. All rights reserved.

**Trademark statement:** The product names and corporate logos of Bat Wireless appearing in this manual are the lawful property of our company (including its affiliated entities). Any unauthorized use, reproduction, or imitation is strictly prohibited. Third-party trademarks cited in this manual belong to their respective owners. Their use herein is for descriptive purposes only and does not imply any commercial association or authorization. Our company reserves all rights to pursue legal action against infringement.

**Disclaimer:** The product information contained in this manual is provided for reference only. Actual product performance may vary depending on environmental conditions and configuration differences. Our company makes no express or implied warranties regarding the accuracy, completeness, or applicability of the contents of this manual, and assumes no liability for any direct or indirect losses arising from the use of or inability to use its contents. Users should independently evaluate the applicability of the product and comply with proper operational standards. The final right of interpretation rests with our company.

July-29-2025-A01 2 / 13



### **BWGPSCNX8-8B1**

Part number description			
BW	Company	Bat Wireless	
GPS	Frequency	GPS	
С	Name	Ceramic antenna	
N	Туре	Internal	
X	Constant	X	
8-8	Dimensions	8-8mm	
B1	Connector	IPEX1	

Model sele	ection tab	le					
Connector	IPEX-1	IPEX-2	IPEX-3	IPEX-4	IPEX-5	SMA	Customizable options available
Cable length	25	50	120	200	250	300	Customizable options available
Cable type	RG0.81	RG1.13	RG1.37	RG174	RG178	RG316	Customizable options available

### 1. Product description

The Bat Wireless BWGPSCNX8-8B1 is a ceramic antenna operating at a frequency band of 1575 MHz. Utilizing a specialized ceramic dielectric material, the antenna achieves compact size while maintaining excellent radiation efficiency and low dielectric loss. Featuring low loss and high stability ,the ceramic dielectric exhibits minimal signal attenuation and outstanding temperature stability, making it suitable for automotive, outdoor, and other demanding environments, as well as for low-power applications. Designed with right-

hand circular polarization to match the polarization mode of BeiDou satellite signals,

it provides strong resistance to multipath interference and improves positioning accuracy. Easy to integrate, typically equipped with ANT connection pins and ground pins for convenient soldering or modular design.

Typical Application Scenarios:

Automotive and Transportation Sector: in-vehicle navigation systems, commercial fleet management, and intelligent transportation infrastructure.

Consumer Electronics and Portable Devices: smartphones/tablets, outdoor sports equipment, and shared economy devices

Internet of Things (IoT) and Asset Tracking: logistics tracking and agricultural IoT

Aerospace and Defense: unmanned aerial vehicles (UAVs), satellite communication terminals, and military equipment.

Bat Wireless provides customized services to optimize your devices. With a well-established R&D team, we can respond quickly to meet your specific requirements. If you have any requests, please contact our sales representatives or FAE.

July-29-2025-A01 3 / 13



# 2. Product specification

Parameters	Typical value	Units	Notes	
Electrical characteristics				
Antenna type	Ceramic antenna			
Frequency range	1575±5	MHz		
Input impedance	50	Ω		
V.S.W.R (voltage standing wave ratio)	<2			
Passive antenna gain	0.6	dBi		
LNA gain	21.5	dBi		
Polarization type	Right-hand circular polarization (RHCP)			
Power capacity	50	W		
Current consumption	4.3	mA		
DC voltage	1.8-3.6	V		
Mechanical characteristics				
Dimensions	8 x 8 x 6.5	mm		
Connector type	IPEX-1 (customizable)			
Cable type	RG1.13 (customizable)			
Cable length	120 (customizable)	mm		
Mounting method	Press-fit			
Color	Silver white			
Material	Ceramic			
Weight	2.94	g		
Environmental characteristics				
Waterproof rating	-			
RoHS compliant	Complies			
Operating temperature	-45~ +85	°C		
Storage temperature	-45~ +85	°C		

July-29-2025-A01 4 / 13



# 3. Physical diagram / dimensions




Images are for reference only; the actual product shall prevail.

July-29-2025-A01 5 / 13



### 4. Dimensional drawing / mechanical drawing



July-29-2025-A01 6 / 13



# 5. Test equipment







R&S / CMW500 communication tester



R&S / SMBV100B signal generator




# DT-3500 Datasheet / System SpecificationsSpecification:DescriptionTest frequency range400MHz-8.5GHzSystem sizeL\*W\*H=4\*3.5\*3.5mNumber of probes23 (Probe) + 1 (link)Interval angle15°Sampling diameter2200mmCarrying capacity≤40kg

Testing capability	Description / capability description
Active measurement Active testing	Capability / Test metrics: TRP, TIS, EIRP, EIS, etc.  Mode / Test standards: 2G / 3G / 4G / 5G, Wi-Fi b/g/n/a/ac/ax, BT, NB-IoT, Cat-M (eMTC), GPS / BEIDOU / GLONASS, ZigBee, LoRa (Non-Signaling),.etc
Passive measurement Passive testing	<b>Test types:</b> Gain, efficiency, 2D pattern, 3D pattern, pattern roundness, axial ratio, ECC, phase center, etc <b>Polarization type:</b> Circular polarization, linear polarization, elliptical polarization


July-29-2025-A01 7 / 13








### RF link diagram of multi-probe spherical near-field testing system



# 

# RF link overview SET TO THE STATE OF THE ST




RF link of passive measurement

July-29-2025-A01 8 / 13




### 6. Performance data

### 6.1 Voltage standing wave ratio (VSWR)



### 6.2 Return loss




July-29-2025-A01 9 / 13




### 6. Performance data

### 6.3 **Gain**



### 6.4 Efficiency





### 6.5 Antenna gain and efficiency


Frequency (MHz)	1570	1575	1580
Maximum gain (dBi)	0.2	0.55	-1.32
Efficiency (%)	35.56	39.54	29.85


July-29-2025-A01 10 / 13





# 7. Radiation patterns

### 7.1 2D Radiation pattern diagram










July-29-2025-A01 11 / 13



### 7.2. 3D radiation pattern diagram




July-29-2025-A01 12 / 13



Documentation	
Version:	July-29-2025-A01
Date:	2025-7-29
Remarks	Initial release
Author:	Carly

Change Log	

July-29-2025-A01 13 / 13



www.batwireless.com

Shenzhen Bat Wireless Technology Co., Ltd.

Address: Room 1301, No. 8 Langhua Road, Xinshi Community, Dalang Street, Longhua District, Shenzhen

Email: marketing@batwireless.com

Tel: +86-0755-21031236