







ROHS

技术要求:

Technical requirements:

1. 表面光洁, 平整无毛刺;

The surface is smooth and smooth without burr;

2. 参数/批次字迹清晰, 无错位;

Clear handwriting of parameters/batches without any dislocation;

3. 额定电压: 1th: 2A Ui: 250V;

Rated voltage: 2A Ui: 250V;

4. 工作温度: -25℃~+65℃;

Working environment temperature: -25℃~+65℃;

5. 动作形式: 自锁式;

Action form: self-locking ;

6. 动作行程: 约3mm;

Movement stroke: about 3mm

7. 连接形式: 配套接插件/焊接导线;

Connection form: supporting connector/welding wire;

8. 拧紧力矩: 5~14Nm;

Tightening torque: 5-14nm;

9. 开关组合: 1NO;

Switch combination: 1NO;

10. 外观材料: 按键: 黄铜/不锈钢;

外壳: 黄铜/不锈钢;

底座: PBT;

Appearance material: Keypad: Brass/stainless steel;

Case: Brass/stainless steel;

Pedestal: PBT;

11. 未标注公差按照GB/T 1804-m级。

Unmarked tolerance shall be in accordance with GB/T 1804 f class.

性能要求:

Performance requirements:

1. 防护等级: IP65;

Protection grade: IP65.

2. 接触电阻: ≤50mΩ

Contact resistance: ≤50mΩ.

3. 绝缘电阻: ≥100MΩ

The insulation resistance: ≥100MΩ

4. 抗电强度: AC2500V, 1min, 无闪烁、击穿;

Electrical resistance: AC2500V, 1min, no

flicker and breakdown;

5. 寿命: 电气部分在额定负载下动作5万次无异常。

Life: electrical part: operate 50,000 times

under rated load without any abnormality.

机械部分: 动作50万次无异常;

Mechanical part: no abnormal movement for 500,000times.

MATERIAL:

Actuator: SUS ;

Top Base: SUS;

Bottom Base: PA66+GF ;

Terminal: Brass, Silver plated ;

Nut: Brass, Ni plated .


The material contained in this drawing is the property of XiBang. Any use other than that specifically authorized by XiBang is prohibited. The above drawing is subjected to change for improvement without prior notice.



东莞市溪榜电子有限公司
DONG GUAN XI BANG ELECTRONICS CO., LTD

TITLE : METAL PUHS BUTTON SWITCH

MODEL : XB-PBM19-11Z-R2-NNN-S0-S



TOLERANCE
<=1.5mm±0.1
> 1.5mm±0.2
>=10mm±0.3

ANGLE
±2°

UNIT : MM	DWN.	ZENQ. CHEN	DATE	
SCALE : 3 : 1	CHK'D	PENG. GAO	DATE	
VBRSION	01	APPD.	FEI. LONG. HE	DATE

7	SPRING	STEEL WIRE	1	NATURE
6	STEEL BALL	STEEL	1	NATURE
5	BOARD	PHENOLIC RESIN	1	NATURE
4	CONTACT CLIP	PBS STRIP	2	Ag PLATED
3	FRAME	IRON STRIP	1	Ni PLATED
2	TERMINAL	BRASS STRIP	8	Ag PLATED
1	KNOB	POM	1	BLACK
NO.	PART NAME	MATERIAL	QTY.	FINISHING