



产品承认书
SPECIFICATION FOR APPROVAL

客户名称: CUSTOMER _____

我司料号: XRT1264-103VFRL4
OUR PART NO. _____

我司品名: Magneticringcommonmodechoke
OUR PART NAME _____

送样日期: _____ 数量: _____
DATE SAMPLES _____ QUANTITY _____

制造确认 MANUFACTURER APPROVE		
拟制 DRAWN	审核 CHECKED	确认 APPROVED
LiuJialing	RaoPing	ZhongCuilan

客户确认 CUSTOMER APPROVE

客户名称 CUSTOMER NAME: _____

客户料号 CUSTOMER P/N: _____

规格型号 DESCRIPTION: 12*6*4commonmodechoke>10mH0.4lineSeparatewinding
Partitiondispensing

检查结果: ☐ 合格 ☐ 不合格 签名及盖章: _____

INSPECT RESULT ACCEPT REJECT SIGNATURE AND STAMP

说明 REMARK: _____

如对本承认书内容有异议请提出或标记发送至我司，本承认书在未收到异议回复时于本承认书提供一周后生效。

Ifyou have any objection to the contents of this acknowledgment, please raise it or send the mark to us. The acknowledgment will become effective one week after the acknowledgment is provided in the absence of any objection.

东莞市祥如电子有限公司

DONGGUANXIANGRUELECTRONICSCO.,LTD

Tel: 0769-86346548 Fax: 0769-86346358

Email: dgxiangru@126.com



修订记录 Revision record

[illegible]


产品承认书

SPECIFICATION FOR APPROVAL

客户名称 CUSTOMER		日期 DATE	2024/5/29
客户物料编号 CUSTOMER P/N		客户规格型号 DESCRIPTION	12*6*4common mode choke>10m H 0.4line Separate winding Partition dispensing
我司物料编号 OUR PART NO	XRT1264-103VFRL4	我司品名 OUR PART NAME	Magneticringcommon modechoke

外观尺寸 Appearance of size


单位 Unit: mm



A	13.7MAX	C	10.0±1.0	E	9.0 ±1.0		
B	6.5 MAX	D	0.4 REF				
标识Identification							

(以上尺寸为手工测量只做参考详细尺寸以实物为准)

电路图 Schematic Diagram



绕线结构表 Winding Structure Diagram

绕组 WINDING	起始 S	结束 F	绝缘线/漆包线 WIRE	圈数 TURNS		绕制方式 WINDINGWAY		
N1	1	2	2UEW Φ0.4mm	29TS	参考refer	平整密绕		
N2	4	3	2UEW Φ0.4mm	29TS	参考refer	平整密绕		

1.绕线须紧密均匀平整，铜线不可破皮现象。1. The winding shall be tight, even and flat, and the copper wire shall not be broken.



产品承认书

SPECIFICATION FOR APPROVAL

客户名称 CUSTOMER		日期 DATE	2024/5/29			
客户物料编号 CUSTOMER P/N		客户规格型号 DESCRIPTION	12*6*4commonmodechoke >10mH0.4lineSeparate windingPartitiondispensing			
我司物料编号 OUR PART NO	XRT1264-103VFRL4	我司品名 OUR PART NAME	Magneticringcommon modechoke			
电性参数 Electrical parameters						
测试项目 TEST PROJECT	电性范围 SPEC	测试条件 TEST FREQ	测试仪器 TEST STRUMENTS			
电感量L1	>10mH	at 25°C 1KHz/0.3V	TH2829A			
电感量L2	>10mH	at 25°C 1KHz/0.3V	TH2829A			
额定电流Irms	1.2A (±5%)	电路板实测	E1412A			
峰值(瞬间)电流Peak (instantaneous) current	1.2A-4A (±5%)	电路板实测	E1412A			
测试报告 The test report						
测试项目 Test project	电性范围 Spec	测试结果 Test result				
		1	2	3	4	5
电感量L1	>10mH	OK	OK	OK	OK	OK
电感量L2	>10mH	OK	OK	OK	OK	OK
额定电流Irms	1.2A (±5%)	OK	OK	OK	OK	OK
峰值(瞬间)电流Peak (instantaneous)	1.2A-4A (±5%)	OK	OK	OK	OK	OK
测试室温/湿度: 室温: 25°C(REF) 对湿度: 80%(REF) 工作温度: -45°C ~ +125°C TEST CONDITION:TEMP:25°C(REF) R.H.: 80%(REF) Operation Temperature Range: - 45°C ~+125°C						
NO	项目project	技术要求technical requirement	结论			
1	外观和尺寸 Appearance and size	符合产品规范和公差要求 Meet product specifications and tolerance requirements.	OK			
2						
制表 MADE		审核 CHECKED	批准 APPROVE			
Liu Jialing		RaoPing	ZhongCuilan			



注意事项 Matters needing attention

1、本公司产品适用于 AV 设备、OA 设备、家电、信息服务等一般电子设备中。

Our products are designed and promoted for use in general electronic devices such as audio-video equipment, office automation equipment, home appliance and information service.

2、当本公司的产品使用在一般电子设备以外的领域时，对于此所引发的设备失效我司将不承担任何法律责任。

In case of using the product for the purpose other than general electronics devices, we shall not be held liable for any dysfunctions in or damage to the equipment with which the product is used.

3、本承认书只保证我司产品作为一个单体时的质量情况，当我司产品被安装到贵司产品上时，请贵司对使用在贵司电路上的产品情况进行了有效评价和确认。

Our specification limits the quality of the component as a single unit. Please ensure the component is thoroughly evaluated in your application circuit.

4、不要对产品施加过大的振动或机械冲击；

Do not apply excessive vibration or mechanical shock to products.

5、为防止断线，请不要使用锋利的物体接触线圈，如镊子；

Do not touch wire with sharp objects such as tweezers to prevent wire breakage.

6、在产品贴装时不要使用过大的压力，避免磁芯断裂。

Do not apply excessive stress to products mounted on boards to prevent core breakage.

7、为保证端子电极的焊接特性和包装材料处于良好状态，请于本公司发货后 6 个月内使用本产品。同时，由于端子电极的焊接特性会随时间发生变化，如果贮存时间超过 6 个月，请首先确认其焊接特性后再安装使用。

To maintain the solderability of terminal electrodes and to keep the packing material in good condition, product should be used within 6 months from the time of delivery. And the solderability of products electrodes may decrease as time passes, so in case of storage over 6 months, solderability

8、存放货物的仓库应满足以下条件 Store products in a warehouse in compliance with the following condition:

条件 Conditions	元件含包装物 Packing status	元件自身 Component itself
温度 Temperature	-25~+40℃	-25~+85℃
湿度 Humidity	30~70%RH	30~70%RH

9、不要使产品遭受温度和湿度的快速变化。

Do not subject products to rapid changes in temperature and humidity.

10、不要将产品存放在化学环境中，如硫酸气体或碱性气体中，否则会降低电极端子的焊接特性和使电感器腐蚀。

Do not store the products in chemical atmosphere such as one containing sulfurous acid gas or alkaline gas, that will causes poor solderability and corrosion of inductors.

11、为了避免受潮气、灰尘等物质的影响，产品应保管于货架上。

Store products on pallets to protect from humidity, dust, etc

12、产品应避免热冲击、振动以及直接光照等等。

Avoid heat shock, vibration, direct sunlight, etc.