






SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 500V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)



P/N	PIN	DIM.A	DIM.B
PZ2.0-US2S-01A-R	2*1	0.00	2.00
PZ2.0-US2S-02A-R	2*2	2.00	4.00
PZ2.0-US2S-03A-R	2*3	4.00	6.00
PZ2.0-US2S-04A-R	2*4	6.00	8.00
PZ2.0-US2S-05A-R	2*5	8.00	10.00
PZ2.0-US2S-06A-R	2*6	10.00	12.00
PZ2.0-US2S-07A-R	2*7	12.00	14.00
PZ2.0-US2S-08A-R	2*8	14.00	16.00
PZ2.0-US2S-09A-R	2*9	16.00	18.00
.....			
PZ2.0-US2S-40A-R	2*40	(PIN-1)x2.0	(PIN)x2.0

RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ± 0.05 (TOP VIEW)

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X ± 0.35	X.* $\pm 5^\circ$	APR.	Alex	TITLE: 2.0PH H2.0 2xnPin SMT PC6.5 PA3.8 PB2.5 L8.0 6T	
.XX ± 0.25	.X.* $\pm 3^\circ$	CHK.	Jack	DWG NO. PZ2.0-US2S-NA-R	
.XXX ± 0.15	.XX.* $\pm 1^\circ$	DRA.	Can	PROJ.	CUSTOMER DRAWING
		SIZE A4	SCALE 1:1	SHEET 1/1	REV. A