







SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 500V
Operation Temperature: -40 $^{\circ}$ to+105 $^{\circ}$
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240 $^{\circ}$ C for30-60seconds
(260 $^{\circ}$ C for 5 seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)

P/N	PIN	DIM.A	DIM.B
PM2.0-US2S-01A-R	1	0.00	2.00
PM2.0-US2S-02A-R	2	2.00	4.00
PM2.0-US2S-03A-R	3	4.00	6.00
PM2.0-US2S-04A-R	4	6.00	8.00
PM2.0-US2S-05A-R	5	8.00	10.00
PM2.0-US2S-06A-R	6	10.00	12.00
PM2.0-US2S-07A-R	7	12.00	14.00
PM2.0-US2S-08A-R	8	14.00	16.00
PM2.0-US2S-09A-R	9	16.00	18.00
.....			
PM2.0-US2S-40A-R	40	(PIN-1)x2.0	(PIN)x2.0

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.3	X.*± 5°	APR.	Alex	TITLE: 2.0FH H4.3 2xnPin SMT W4.5 U# PC6.5 PB4.6 6T	
.XX±0.2	.X.*± 3°	CHK.	Jack	DWG NO. PM2.0-US2S-NA-R	
.XXX±0.1	.XX*± 0.5	DRA.	Can	PROJ.	CUSTOMER DRAWING
				SIZE A4	SCALE 1:1