


## RBE011N08R1SZPW-VB Datasheet

### N-Channel 100 V (D-S) MOSFET

PRODUCT SUMMARY			
$V_{DS}$ (V)	$R_{DS(on)}$ ( $\Omega$ ) MAX.	$I_D$ (A)	$Q_g$ (TYP.)
100	0.0012 at $V_{GS} = 10$ V	415	130 nC

#### FEATURES

- SGT technology Power MOSFET
- Maximum 175°C junction temperature
- 100 %  $R_g$  and UIS tested



#### APPLICATIONS

- Power supplies:
  - Uninterruptible power supplies
  - AC/DC switch-mode power supplies
  - Lighting
- Synchronous rectification
- DC/DC converter
- Motor drive switch
- DC/AC inverter
- Solar micro inverter
- Class D audio amplifier

ABSOLUTE MAXIMUM RATINGS ( $T_C = 25$ °C, unless otherwise noted)				
PARAMETER		SYMBOL	LIMIT	UNIT
Drain-Source Voltage		$V_{DS}$	100	V
Gate-Source Voltage		$V_{GS}$	$\pm 20$	
Continuous Drain Current ( $T_J = 150$ °C)	$T_C = 25$ °C	$I_D$	415	A
	$T_C = 100$ °C		296	
Pulsed Drain Current ( $t = 100$ $\mu$ s)		$I_{DM}$	1500	
Avalanche Current	$L = 0.5$ mH	$I_{AS}$	100	
Single Avalanche Energy <sup>a</sup>		$E_{AS}$	2500	
Maximum Power Dissipation <sup>a</sup>	$T_C = 25$ °C	$P_D$	455 <sup>b</sup>	W
	$T_C = 100$ °C		227 <sup>b</sup>	
Operating Junction and Storage Temperature Range		$T_J, T_{stg}$	-55 to +175	°C

THERMAL RESISTANCE RATINGS				
PARAMETER		SYMBOL	LIMIT	UNIT
Junction-to-Ambient (PCB Mount) <sup>c</sup>		$R_{thJA}$	62	°C/W
Junction-to-Case (Drain)		$R_{thJC}$	0.33	







#### Notes


- Duty cycle  $\leq 1$  %.
- See SOA curve for voltage derating.
- When mounted on 1" square PCB (FR4 material).

SPECIFICATIONS ( $T_J = 25^\circ\text{C}$ , unless otherwise noted)						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNIT
<b>Static</b>						
Drain-Source Breakdown Voltage	$V_{DS}$	$V_{GS} = 0\text{ V}$ , $I_D = 250\text{ }\mu\text{A}$	100	-	-	V
Gate Threshold Voltage	$V_{GS(\text{th})}$	$V_{DS} = V_{GS}$ , $I_D = 250\text{ }\mu\text{A}$	2	3	4	
Gate-Body Leakage	$I_{GSS}$	$V_{DS} = 0\text{ V}$ , $V_{GS} = \pm 20\text{ V}$	-	-	$\pm 250$	nA
Zero Gate Voltage Drain Current	$I_{DSS}$	$V_{DS} = 80\text{ V}$ , $V_{GS} = 0\text{ V}$	-	-	1	$\mu\text{A}$
		$V_{DS} = 80\text{ V}$ , $V_{GS} = 0\text{ V}$ , $T_J = 125^\circ\text{C}$	-	-	100	
		$V_{DS} = 80\text{ V}$ , $V_{GS} = 0\text{ V}$ , $T_J = 150^\circ\text{C}$	-	-	5	mA
On-State Drain Current <sup>a</sup>	$I_{D(\text{on})}$	$V_{DS} \geq 10\text{ V}$ , $V_{GS} = 10\text{ V}$	150	-	-	A
Drain-Source On-State Resistance <sup>a</sup>	$R_{DS(\text{on})}$	$V_{GS} = 10\text{ V}$ , $I_D = 60\text{ A}$	-	0.0012	-	$\Omega$
		$V_{GS} = 7.5\text{ V}$ , $I_D = 50\text{ A}$	-	0.0015	-	
Forward Transconductance <sup>a</sup>	$g_{fs}$	$V_{DS} = 25\text{ V}$ , $I_D = 100\text{ A}$	-	260	-	S
<b>Dynamic <sup>b</sup></b>						
Input Capacitance	$C_{iss}$	$V_{GS} = 0\text{ V}$ , $V_{DS} = 50\text{ V}$ , $f = 1\text{ MHz}$	-	11500	-	pF
Output Capacitance	$C_{oss}$		-	3246	-	
Reverse Transfer Capacitance	$C_{rss}$		-	18	-	
Total Gate Charge <sup>c</sup>	$Q_g$	$V_{DS} = 50\text{ V}$ , $V_{GS} = 10\text{ V}$ , $I_D = 20\text{ A}$	-	130	-	nC
Gate-Source Charge <sup>c</sup>	$Q_{gs}$		-	50	-	
Gate-Drain Charge <sup>c</sup>	$Q_{gd}$		-	30	55	
Gate Resistance	$R_g$	$f = 1\text{ MHz}$	-	0.8	1.2	$\Omega$
Turn-On Delay Time <sup>c</sup>	$t_{d(\text{on})}$	$V_{DD} = 50\text{ V}$ , $R_L = 5\Omega$ $I_D \equiv 50\text{ A}$ , $V_{GEN} = 10\text{ V}$ , $R_g = 1\Omega$	-	33	-	ns
Rise Time <sup>c</sup>	$t_r$		-	30	-	
Turn-Off Delay Time <sup>c</sup>	$t_{d(\text{off})}$		-	50	-	
Fall Time <sup>c</sup>	$t_f$		-	55	-	
<b>Drain-Source Body Diode Ratings and Characteristics <sup>b</sup> (<math>T_C = 25^\circ\text{C}</math>)</b>						
Pulsed Current ( $t = 100\text{ }\mu\text{s}$ )	$I_{SM}$	$I_F = 500\text{ A}$ , $V_{GS} = 0\text{ V}$	-	-	480	A
Forward Voltage <sup>a</sup>	$V_{SD}$		-	0.75	1.2	V
Reverse Recovery Time	$t_{rr}$		-	140	280	ns
Peak Reverse Recovery Charge	$I_{RM(\text{REC})}$		-	11	20	A
Reverse Recovery Charge	$Q_{rr}$		-	0.3	0.8	$\mu\text{C}$


**Notes**

- a. Pulse test; pulse width  $\leq 300\text{ }\mu\text{s}$ , duty cycle  $\leq 2\text{ \%}$ .
- b. Guaranteed by design, not subject to production testing.
- c. Independent of operating temperature.


**TYPICAL CHARACTERISTICS** ( $T_C = 25^\circ\text{C}$ , unless otherwise noted)





Source-Drain Diode Forward Voltage




On-Resistance vs. Gate-to-Source Voltage





Threshold Voltage




Transconductance



Safe Operating Area, Junction-to-Ambient

Current Derating <sup>a</sup>


Drain Source Breakdown vs. Junction Temperature



Power, Junction-to-Case

**Note**


- a. The power dissipation  $P_D$  is based on  $T_J$  max. = 25 °C, using junction-to-case thermal resistance, and is more useful in settling the upper dissipation limit for cases where additional heatsinking is used. It is used to determine the current rating, when this rating falls below the package limit.

**THERMAL RATINGS** ( $T_C = 25^\circ\text{C}$ , unless otherwise noted)

**Note**

- The characteristics shown in the two graphs
  - Normalized Transient Thermal Impedance Junction to Ambient ( $25^\circ\text{C}$ )
  - Normalized Transient Thermal Impedance Junction to Case ( $25^\circ\text{C}$ )

are given for general guidelines only to enable the user to get a “ball park” indication of part capabilities. The data are extracted from single pulse transient thermal impedance characteristics which are developed from empirical measurements. The latter is valid for the part mounted on printed circuit board - FR4, size 1" x 1" x 0.062", double sided with 2 oz. copper, 100 % on both sides. The part capabilities can widely vary depending on actual application parameters and operating conditions.

## Package Outlines



UNIT : mm

SYMBOLS	A	A1	A2	A3	b	b1	C	D
MIN	2.25	1.00	0.01	1.50REF	0.68	0.75	0.45	14.80
NOM	2.30	1.04	0.08		0.70	0.85	0.50	15.00
MAX	2.35	1.08	0.16		0.74	0.95	0.55	15.20
SYMBOLS	D1	D2	D3	E	E1	E2	E3	E4
MIN	10.00	2.40	5.77REF	9.70	9.46REF	9.25REF	8.25REF	8.70REF
NOM	10.10	2.60		9.90				
MAX	10.30	2.80		10.10				
SYMBOLS	e	H	H1	L	P	1	2	
MIN	1.18	5.00	4.40	2.40	2.80	7 °	7 °	
NOM	1.20	5.20	4.60	2.45	3.00	-	-	
MAX	1.22	5.40	4.80	2.50	3.20	9 °	9 °	

## Disclaimer

All products due to improve reliability, function or design or for other reasons, product specifications and data are subject to change without notice.

Taiwan VBsemi Electronics Co., Ltd., branches, agents, employees, and all persons acting on its or their representatives (collectively, the "Taiwan VBsemi"), assumes no responsibility for any errors, inaccuracies or incomplete data contained in the table or any other any disclosure of any information related to the product.(www.VBsemi.com)

Taiwan VBsemi makes no guarantee, representation or warranty on the product for any particular purpose of any goods or continuous production. To the maximum extent permitted by applicable law on Taiwan VBsemi relinquished: (1) any application and all liability arising out of or use of any products; (2) any and all liability, including but not limited to special, consequential damages or incidental ; (3) any and all implied warranties, including a particular purpose, non-infringement and merchantability guarantee.

Statement on certain types of applications are based on knowledge of the product is often used in a typical application of the general product VBsemi Taiwan demand that the Taiwan VBsemi of. Statement on whether the product is suitable for a particular application is non-binding. It is the customer's responsibility to verify specific product features in the products described in the specification is appropriate for use in a particular application. Parameter data sheets and technical specifications can be provided may vary depending on the application and performance over time. All operating parameters, including typical parameters must be made by customer's technical experts validated for each customer application. Product specifications do not expand or modify Taiwan VBsemi purchasing terms and conditions, including but not limited to warranty herein.

Unless expressly stated in writing, Taiwan VBsemi products are not intended for use in medical, life saving, or life sustaining applications or any other application. Wherein VBsemi product failure could lead to personal injury or death, use or sale of products used in Taiwan VBsemi such applications using client did not express their own risk. Contact your authorized Taiwan VBsemi people who are related to product design applications and other terms and conditions in writing.

The information provided in this document and the company's products without a license, express or implied, by estoppel or otherwise, to any intellectual property rights granted to the VBsemi act or document. Product names and trademarks referred to herein are trademarks of their respective representatives will be all.

## Material Category Policy

Taiwan VBsemi Electronics Co., Ltd., hereby certify that all of the products are determined to be RoHS compliant and meets the definition of restrictions under Directive of the European Parliament 2011/65 / EU, 2011 Nian. 6. 8 Ri Yue restrict the use of certain hazardous substances in electrical and electronic equipment (EEE) - modification, unless otherwise specified as inconsistent.(www.VBsemi.com)

Please note that some documents may still refer to Taiwan VBsemi RoHS Directive 2002/95 / EC. We confirm that all products identified as consistent with the Directive 2002/95 / EC European Directive 2011/65 /.

Taiwan VBsemi Electronics Co., Ltd. hereby certify that all of its products comply identified as halogen-free halogen-free standards required by the JEDEC JS709A. Please note that some Taiwanese VBsemi documents still refer to the definition of IEC 61249-2-21, and we are sure that all products conform to confirm compliance with IEC 61249-2-21 standard level JS709A.