





申明: 凡是沒有产品料号或有“PRELIMINARY”标示的产品图均为临时图面暫不能生产 / DECLARATION: ALL PRODUCT DRAWINGS WITHOUT THE PART NUMBER OR WITH "PRELIMINARY" LABEL ARE TEMPORARY DRAWINGS CAN NOT BE PRODUCED

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
C	ECN NO.	MODIFY NOTE	2020.06.23	SYJ
D	ECN NO.	UPDATE THE DRAWING	2020.08.03	SYJ



SECTION:A-A

NOTE:

1.MATERIAL SPECIFICATION:

- 1.HOUSING:HIGH TEMPERATURE RESISTANT PLASTIC,UL94 V-0.
- 2.TERMINAL: COPPER ALLOY(C7025)
- 3.MID PLATE: STAINLESS STEEL(SUS201)
- 4.FRONT SHELL: STAINLESS STEEL(SUS201)

2.PLATING SPECIFICATION:

2-1.TERMINAL:

Ni 50u" MIN. UNDER PLATED OVER ALL.

Au PLATED ON THE FUNCTIONAL AREA OF CONTACT.

(GOLD PLATING THICKNESS FOLLOW THE P/N)

PLATING SPECIFICATIONS OF THE SOLDER AREA FOLLOW THE P/N

2-2.FRONT SHELL:

PLATING SPECIF

PLATING SPECIFICATIONS FOLLOW THE F/N
-3 MID. PLATE PLATE:

2-3. MID PLATE PLATE:
CLEAR ONLY

CLEAR ONLY
MECHANICAL

3.1 INSERTION FORCE: 0.5

- 3-1.INSERTION FORCE: 0.5~2.0kgf.
3-2.REMOVAL FORCE: 0.8kgf~2.0kgf.
3-3.DURABILITY: 10000 CYCLES.

4.ELECTRICAL PERFORMANCE.

- 4-1. VOLTAGE RATING:20 V DC/AC (RMS. max)
CURRENT RATING:5 AMPS. FOR TOTAL VBUS/GND PINS;
1.25AMPS FOR CC PIN,0.25 AMPS. FOR ALL OTHER CONTACT.

- 4-2. LLCR:
VBUS & GND PINS AND OTHER PINS: 40mΩ/PIN MAX.
SHIELD: 50mΩ/MAX.

- LLCR MAX. CHANGE OF ALL PINS: 10mΩ.

- 4-3.INSULATION RESISTANCE: 100MΩ MIN

- 4-4.DIELECTRIC WITHSTAND VOLTAGE,AC 100V FOR 1 MINUTE.

5. ENVIRONMENTAL PERFORMANCE:

OPERATING TEMPERATURE: -25℃~+85℃.

6.IR REFLOW:

THE PEAK TEMPERATURE ON THE BOARD SHALL BE MAINTAINED FOR 10 SECONDS AT 260°C.


7. DATE CODE: XX XX

— WEEK
— YEAR

TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING	浙江创都电子科技有限公司			
X.X ±0.30	X.* ±10*	PART NO.	TITLE: TYPE-C-16P-BS-7.35-3MD-5A			
.XX ±0.20	.X* ± 8*					
.XXX ±0.10	.XX* ± 5*					
UNITS	mm	DESIGN: DRAW	DRAWG NO. DRAW_NO.			
MATERILA		CHED:				
FINISH		APPD:				
			SCALE	SHEET	REV.	
			SCALE	SHEET	REV.	

申明: 凡是没有产品料号或有“PRELIMINARY”标示的产品图均为临时图面都不能生产 / DECLARATION: ALL PRODUCT DRAWINGS WITHOUT THE PART NUMBER OR WITH “PRELIMINARY” LABEL ARE TEMPORARY DRAWINGS CAN NOT BE PRODUCED

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
C	ECN NO.	MODIFY NOTE	2020.06.23	SYJ
D	ECN NO.	UPDATE THE DRAWING	2020.08.03	SYJ



AFTER MATING


USB TYPE-C PIN ASSIGNMENTS

PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND

ORDER INFORMATION

P/N: ACF016-1XXH1A1XX-XHR

HOUSING MATERIAL	D/C
A: LCP	0: WITHOUT D/C
E: PA9T	1: WITH D/C
HOUSING COLOR	CONTACT FUNCTIONAL AREA PLATED
1: BLACK	01: Au 1u"
5: NATURE	03: Au 3u"
SHELL MATERIAL	15: Au 15u"
H: SUS304	30: Au 30u"
N: SK7	CONTACT SOLDER AREA PLATED
SHELL PLATING	1: Au 1u"
1: Ni	CONTACT METRIAL
	A: C1814




RECOMMENDED PCB LAYOUT(TOP VIEW)
THICKNESS 0.80MM:DEFAULT TOLERANCE:±0.05



TOLERANCE		NAME(INTENDED USE)				
		CUSTOMER DRAWING				
X.X	±0.30	X.' ±10'	PART NO.	TITLE:		
.XX	±0.20	.X' ± 8'	DESIGN: DRAW	DRAWG NO.		
.XXX	±0.10	.XX' ± 5'		DRAW_NO.		
UNITS	mm		CHED:		SCALE	SHEET
MATERILA			APPD:		SCALE	SHEET
FINISH					REV.	REV.

申明: 凡是没有产品料号或有“PRELIMINARY”标识的产品图均为临时图面暂不能生产/DECLARATION: ALL PRODUCT DRAWINGS WITHOUT THE PART NUMBER OR WITH "PRELIMINARY" LABEL ARE TEMPORARY DRAWINGS CAN NOT BE PRODUCED

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
C	ECN NO.	MODIFY NOTE	2020.06.23	SYJ
D	ECN NO.	UPDATE THE DRAWING	2020.08.03	SYJ



SEE DETAIL X



PAPER BOARD

REEL AND TAPE

REEL AND TAPE

PAPER BOARD

FOLDER
PAPER BOARD

CARTON

	REEL	CARTON
CONNECTOR (PCS)	1000	15000

TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING						
X.X	±0.30	X.'	±10'	PART NO.	TITLE:			
.XX	±0.20	.X'	± 8'					
.XXX	±0.10	.XX'	± 5'					
UNITS		mm		DESIGN:	DRAW		DRAWG NO.	
MATERILA				CHED:	DRAW_NO.			
FINISH				APPD:		SCALE	SHEET	REV.
					SCALE	SHEET	REV	