



		D		E	
REV.	DESCRIPTION	ECN NO.	NAME	DATE	





SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 500V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for 30-60seconds
(260°C for 5seconds)




RECOMMEND P.C.B LAYOUT

PCB TOLERANCE: ± 0.05 (TOP VIEW)



P/N	PIN	DIM.A	DIM.B
PZ-2.0-2*01-6.0-ZZ	2*1	0.00	2.00
PZ-2.0-2*02-6.0-ZZ	2*2	2.00	4.00
PZ-2.0-2*03-6.0-ZZ	2*3	4.00	6.00
PZ-2.0-2*04-6.0-ZZ	2*4	6.00	8.00
PZ-2.0-2*05-6.0-ZZ	2*5	8.00	10.00
PZ-2.0-2*06-6.0-ZZ	2*6	10.00	12.00
PZ-2.0-2*07-6.0-ZZ	2*7	12.00	14.00
PZ-2.0-2*08-6.0-ZZ	2*8	14.00	16.00
PZ-2.0-2*09-6.0-ZZ	2*9	16.00	18.00
.....			
PZ-2.0-2*40-6.0-ZZ	2*40	(PIN-1)x2.0	(PIN)x2.0

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				BXCONN [®]	
DIM. TOL. x. ±0.30 x.x ±0.25 x.xx ±0.20 GENERAL ANGLE: x° ±5° x.x° ±1° x.xx° ±0.5°		TITLE: 2.0PH H2.0 2xnPin 180度 PC2.8 PA3.9 PB2.0 L8.7 6T					
		DWG. NO.: PZ-2.0-2xN-6.0-ZZ		CHECKED: MAX			
		PART NO.: PZ-2.0-2xN-6.0-ZZ		DRAWN: ELLA			
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL