






SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 500V
Operation Temperature: -40 $^{\circ}$ to+105 $^{\circ}$
Contact Material: Brass
Standard: PA6T
Insrlator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240 $^{\circ}$ C for30-60seconds
(260 $^{\circ}$ C for 5 seconds)



P/N	PIN	DIM.A	DIM.B
PM-2.0-2*01-4.3-ZZ	2*1	0.00	2.00
PM-2.0-2*02-4.3-ZZ	2*2	2.00	4.00
PM-2.0-2*03-4.3-ZZ	2*3	4.00	6.00
PM-2.0-2*04-4.3-ZZ	2*4	6.00	8.00
PM-2.0-2*05-4.3-ZZ	2*5	8.00	10.00
PM-2.0-2*06-4.3-ZZ	2*6	10.00	12.00
PM-2.0-2*07-4.3-ZZ	2*7	12.00	14.00
PM-2.0-2*08-4.3-ZZ	2*8	14.00	16.00
PM-2.0-2*09-4.3-ZZ	2*9	16.00	18.00
.....			
PM-2.0-2*40-4.3-ZZ	2*40	(PIN-1)x2.0	(PIN)x2.0

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					BXCONN [®]	
DIM. TOL. x. ±0.30 x.x ±0.20 x.xx ±0.10		TITLE: 2.0FH H4.3 2xnPin 180度 W4.5 U型 PC2.8 6T						
GENERAL ANGLE: x° ±5' x.x° ±1' x.xx° ±0.5'		DWG. NO.: PM-2.0-2*N-4.3-ZZ			CHECKED: MAX			
		PART NO.: PM-2.0-2*N-4.3-ZZ			DRAWN: ELLA			
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn		