



		D		E	
REV.	DESCRIPTION	ECN NO.	NAME	DATE	





SPECIFICATIONS

Current Rating: 3Amps
 Insulation Resistance: 1000MΩ Min
 Contact Resistance: 20mΩ Max
 Withstanding Voltage: AC 1000V
 Operation Temperature: -40°to+105°
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester(UL 94V-0)
 Contact Plating: Gold Flash
 Max.Processing Temp: 240°C for30-60seconds
 (260°C for5seconds)




RECOMMEND P.C.B LAYOUT

PCB TOLERANCE: ± 0.05 (TOP VIEW)



P/N	PIN	$DIM.A$	$DIM.B$
$PM-2.54-1*01-8.5-WZ$	1	0.00	2.54
$PM-2.54-1*02-8.5-WZ$	2	2.54	5.08
$PM-2.54-1*03-8.5-WZ$	3	5.08	7.62
$PM-2.54-1*04-8.5-WZ$	4	7.62	10.16
$PM-2.54-1*05-8.5-WZ$	5	10.16	12.70
$PM-2.54-1*06-8.5-WZ$	6	12.70	15.24
$PM-2.54-1*07-8.5-WZ$	7	15.24	17.78
$PM-2.54-1*08-8.5-WZ$	8	17.78	20.32
$PM-2.54-1*09-8.5-WZ$	9	20.32	22.86
.....			
$PM-2.54-1*40-8.5-WZ$	40	$(PIN-1) \times 2.54$	$(PIN) \times 2.54$

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				BXCONN [®]	
DIM. TOL. x. ±0.30 x.x ±0.20 x.xx ±0.10 GENERAL ANGLE: x° ±5° x.x° ±1° x.xx° ±0.5°		TITLE: 2.54FH H8.5 1xPin 90度 Y型 PC3.2 PB10.2 6T					
		DWG. NO.: PM-2.54-1*N-8.5-WZ		CHECKED: MAX			
		PART NO.: PM-2.54-1*N-8.5-WZ		DRAWN: ELLA			
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL