




RoHS

VER	MARK	PR. BY	DESCRIPTION	DATE

PIN ASSIGNMENTS

A5	CC1	B12	GND
A9	VBUS	B9	VBUS
A12	GND	B5	CC2
PIN	SIGNAL NAME	PIN	SIGNAL NAME

备注 (NOTE): 1 材质:

1.1 胶芯: LCP UL94 V-0

1.2 端子: (C2680, 镍底, 镀金 0.5U

1.3 外壳: 不锈钢 304-表面镀镍 50U

2. 电气特性:

2.1. 接触区: 接触电阻 30mQMax, 允许 10mΩ 变化量,

测试条件: 20mv, 100mA 下测量,

2.2. 额定电流: 最大 3A

2.3. 额定电压: 5V.

2.4. 耐电电压: 100VAC.

2.5. 绝缘电阻: 至少 100 兆欧

3. 机械性能:

3.1. 插入力: 0.5-2.0Kg

3.2. 拔出力: 0.8-2.0Kg

3.3. 插拔次数: 5000+.

4. 工作环境: -20℃ to +85℃

4.1. 盐雾测试: 24H

GENERAL TOLERANCES
UNLESS SPECIFIED

X.X	±0.30	X.°	±5°
.XX	±0.20	X.X°	±1°
.XXX	±0.10	X.XX°	±0.5°
MANUFACTURE DWG			



深圳市华明通电子有限公司
Shenzhen Huamingtong Electronics Co., Ltd

PART NO.	TITLE:		
HMT-TYPE-C-311D	TYPE-C 6P SMT		
DESIGN: James	CUSTOMER	SIZE	UNITS
CHED: Talen		A4	MM
APPD: Sophia		SCALE	SHEET
		N:A	1/1

