






VER	MARK	PR. BY	DESCRIPTTON	DATE



- Specification:**
- 1. Electrical Characteristics:**
Contact Current Rating: 0.5 Amperes.
Dielectric Withstanding Voltage: AC500V r. m. s.
Insulation Resistance: 1000 M Ω Minimum.
Contact Resistance: 40 m Ω Maximum.
 - 2. Environmental:**
Operating Temperature: -25° C~+90° C.
 - 3. Environmental:**
Mating Cycles: 5,000 Insertions.
 - 4. Mechanical Characteristics:**
Card Push Insertion/Out Force: 0.2~1.40kgf.
Contact Separation Force: 0.20kgf Minimum.
 - 5. Material:**
Insulator: HI-Temp Plastic UL 94V-0 Rated.
Contact: Copper Alloy (t=0.15mm).
Shell: Stainless Steel (t=0.15mm).
Spring: SWP.
Salt spray time: 24H




 PAD AREA


 KEEP OUT AREA

Circuit Diagram for Detect Switch


WITHOUT CARD	OPEN	CD GND (S)
INSERTING CARD	CLOSE	CD GND (S)

PIN NO.	NAME	TYPE	DESCRIPTION
1	DAT2	I/O/PP	DATE LINE(BIT2)
2	CD/DAT3	I/O/PP	CARD DETECT DATE LIN(BIT3)
3	CMD	PP	COMMAND RESPONSE
4	VDD	S	SUPPLY VOLTAGE
5	CLX	I	CLOCK
6	VSS	S	SUPPLY VOLTAGE GROUND
7	DATO	I/O/PP	DATE LINE(BIT0)
8	DAT1	I/O/PP	DATE LINE(DIT1)

GENERAL TOLERANCES UNLESS SPECIFIED			H HMT CONN 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd			
.X ±0.35	.X° ±3°	PART NO. HMT-TF-015	TITLE: MICRO SD CARD PUSH PUSH SMT 镀金 双压片 外焊			
.XX ±0.25	.XX° ±2°					
.XXX ±0.15		DESIGN: James	CUSTOMER	SIZE	UNITS	
MANUFACTURE DWG		CHED: Talen		A4	MM	
		APPD: Sophia			SCALE	SHEET
				N:A	1/1	



1. 材质要求:
- 1.1 纸箱的材质为K=K;外形尺寸为34*34*32.
 - 1.2 卷盘的材质为PS,卷盘的外形尺寸为 $\phi 330*30.4$;
2. 包装方式:
- 2.1 将卷带放入包装机后,前空5PCS,后放产品1000PCS,
 - 2.2 将包装好的产品从包装机上取下并包装好,贴上内盘标签;
 - 2.3 把累叠好的7盘叠放入纸箱中共计7Kset,上下放纸板;
 - 2.4 把包装好的成品打包封箱,并在纸箱外贴上标签

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd		
.X ±0.35	.X° ±3°	PART NO. HMT-TF-015	TITLE: MICRO SD CARD PUSH PUSH SMT 镀金 双压片 外焊	
.XX ±0.25	.XX° ±2°			
.XXX ±0.15		DESIGN: James	CUSTOMER	SIZE
MANUFACTURE DWG		CHED: Talen		UNITS
		APPD: Sophia		MM
				SCALE
				SHEET
				N:A
				1/1