






SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)



P/N	PIN	DIM.A	DIM.B
PZ-2.54-2*01-8.5-SM	2*1	0.00	2.54
PZ-2.54-2*02-8.5-SM	2*2	2.54	5.08
PZ-2.54-2*03-8.5-SM	2*3	5.08	7.62
PZ-2.54-2*04-8.5-SM	2*4	7.62	10.16
PZ-2.54-2*05-8.5-SM	2*5	10.16	12.70
PZ-2.54-2*06-8.5-SM	2*6	12.70	15.24
PZ-2.54-2*07-8.5-SM	2*7	15.24	17.78
PZ-2.54-2*08-8.5-SM	2*8	17.78	20.32
PZ-2.54-2*09-8.5-SM	2*9	20.32	22.86
.....			
PZ-2.54-2*40-8.5-SM	2*40	(PIN-1)X2.54	(PIN)X2.54

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				BXCONN® 		
DIM.	TOL.	TITLE: 2.54PH H2.5 2xnPin SMT						
x.	±0.30	PC7.5 PA6.0 PB3.2 L11.0 6T						
x.x	±0.20	DWG. NO.: PZ-2.54-2*N-8.5-SM		CHECKED: MAX				
x.xx	±0.10	PART NO.: PZ-2.54-2*N-8.5-SM		DRAWN: ELLA				
GENERAL ANGLE:		UNIT: mm		SCALE: none	SHEET: 1 of 1			DWG. SIZE: A4
x°	±5°							
x.x°	±1°							
x.xx°	±0.5°							