




REV.	DESCRIPTION	ECN NO.	NAME	DATE



SPECIFICATIONS
 Current Rating:1.0 Amps
 Withstanding Voltage:AC 500V
 Insulation Resistance:1000MΩ Min
 Contact Resistance:20mΩ Max
 Operation Temperature:-40° to+105°
 Insrlator Material:Polyester(UL94V-0)
 Contact Material:Brass
 Standard:PA6T
 Contact Plating:Gold Flash
 Max.Processing Temp: 240°C for30-60seconds
 (260°C for5seconds)



P/N	PIN	$DIM.A$	$DIM.B$
PZ-1.27-2*01-5.0-SM	2*1	0.00	1.27
PZ-1.27-2*02-5.0-SM	2*2	1.27	2.54
PZ-1.27-2*03-5.0-SM	2*3	2.54	3.81
PZ-1.27-2*04-5.0-SM	2*4	3.81	5.08
PZ-1.27-2*05-5.0-SM	2*5	5.08	6.35
PZ-1.27-2*06-5.0-SM	2*6	6.35	7.62
PZ-1.27-2*07-5.0-SM	2*7	7.62	8.89
PZ-1.27-2*08-5.0-SM	2*8	8.89	10.16
PZ-1.27-2*09-5.0-SM	2*9	10.16	11.43
.....			
PZ-1.27-2*50-5.0-SM	2*50	$(PIN-1) \times 1.27$	$(PIN) \times 1.27$

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					BXCONN [®]	
DIM. TOL. x. ±0.30 x.X ±0.25 x.XX ±0.20 GENERAL ANGLE: x ° ±5° x.X ° ±1° x.XX ° ±0.5°		TITLE: 1.27PH H1.0 2xnPin SMT W3.4 PC5.5 PA4.0 PB1.5 L7.2 6T						
		DWG. NO.: PZ-1.27-2*N-5.0-SM			CHECKED: MAX			
		PART NO.: PZ-1.27-2*N-5.0-SM			DRAWN: ELLA			
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL	