


GT-TD037B-H026-L1

G-Switch

Operating Force

A=160gf
B=250gf
D=300gf



Switch Height(mm)

H026=2.6

Switch Lifetime

L1=100,000 Cycles
L2=200,000 Cycles

Keying Tip Tilt




RECOMMENDED PCB LAYOUT
TOLERANCE:±0.05

G-Switch Specification:

- 1. Operating temperature range: -40°C ~ +85°C
- 2. Rating: 50mA, 12V DC
- 3. Insulation resistance: 100MΩ min, 100V DC
- 4. Dielectric strength: 250V AC for 1 min
- 5. Contact resistance: 100mΩ max.
- 6. Travel: 0.15±0.1mm

6	STEM	PPA	BLACK
5	COVER	SUS304	Sn PLATED
4	TAPE	POLYIMIDE	YELLOW (TRANSPARENT)
3	CONTACT	STAINLESS STEEL 301	Ag PLATED
2	BASE	PA9T	BLACK
1	TERMINAL	C5210	Ag PLATED
NO.	PART NAME	MATERIAL	REMARK



CIRCUIT DIAGRAM



SCALE: 1:1 UNIT: mm
SIZE: A4

Unless otherwise
General Tolerance:
X. ±0.30
X.x ±0.20
X.xx ±0.10
X* ±3°

Title: Horizontal Tact Switch Mid-Mount 2.1
SMT CH=-0.63 5.55×2.90×H2.6mm

Molde Code: GT-TD037B-H026-L1

DRAWN	CHECKED	APPROVED	DATE
Jiang	Xia	Chen	2024.03.10

品赞科技
www.dg-switch.com

REV: A0

SHEET: 1/1