








RoHS




NOTE:1
1. ELECTRICAL CHARACTERISTICS:
1.1 CURRENT RATING: 0.5A MAX.
1.2 IMPEDANCE:500HM NOMINAL.
2. MECHANICAL CHARACTERISTICS:
2.1 OPERATING TEMP. -40°~90°
2.2 VEWR UP TO 3GHz:1.3MAX.
3GHz TO 6GHz:1.4MAX.
2.3 DURABILITY:30CYCLES

NOTE:2
1.HOUSING MATERIAL: LCP, NATURE, UL94V-0.
2.TERMINAL MATERIAL: COPPER ALLOY (C2680),
3.SHELL MATERIAL: COPPER ALLOY (C5191),



RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ±0.05

3	GROUND CONTACT	1	COPPER ALLOY	Au PLATING OVER NI OVER ALL	
2	INNER CONTACT	1	COPPER ALLOY	Au PLATING OVER NI OVER ALL	
1	HOUSING	1	LCP UL94V-0		
ITEM	DESCRIPTION	Q'TY	MATERIAL	FINISH	REMARK

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd	
X.X ±0.30	X.* ±5°	PART NO. HMT-U.FL-R-SMT	TITLE: IPEX 内针
.XX ±0.20	X.X* ±1°	DESIGN: James	CUSTOMER
.XXX ±0.10	X.XX* ±0.5°	CHED: Talen	SIZE A4
MANUFACTURE DWG		APPD: Sophia	UNITS MM
			SCALE N:A
			SHEET 1/1