










Pin No.	NAME
1	DAT2
2	CD/DAT3
3	CMD
4	VDD
5	CLK
6	VSS
7	DAT0
8	DAT1



RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ± 0.05

NOTES

1.Electrical:

Contact resistance:50m ohms max.
Dielectric withstanding voltage:500V RMS.
Insulation resistance:1000M ohms min.

2.Mechanical:

MATE AND UNMATE FORCE:
MATE FORCE:3.5kg MAX
UNMATE FORCE:0.05kg MIN
Durability:1500cycles MIN.

3.Environment:

Operating Temperature:-25°to+85°.

4.FINISH:

TERMINAL: C5191 GOLD Plated Over NICKEL
Contact area,
Plated ALL Over NICKEL.

Shell: SUS201 WITH NICKEL&GOLD Plated.

5.COLOR:

HOUSING:LCP,BLACK.


DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 2.65H TF无焊PIN	
.XX ± 0.2	.X $\pm$	CHK.	Jack	DWG NO. XY-TF-021B-H265	
.XXX ± 0.1	.XX $\pm$	DRA.	Can	PROJ.	CUSTOMER DRAWING
SIZE A4	SCALE 1:1	SHEET 1/1	REV. A		

User Direction of Unreeling
→

REV.	Q'TY	ECN. NO.	APR.	DATE

NOTES

1. NUMBER OF CONNECTORS:SEE TABLE 2
2. LEAD TAPE LENGTH



3. QUANTITY: 10 REEL/CARTON


COVER TAPE PEELING ANGLE: 165°~180°
PEELING FORCE: 20~130g

CARRIER TAPE

User Direction of Unreeling
→

DETAIL B

DETAIL B



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 2.65H TF 贴片 PIN	
.X±0.3	X.*±2	CHK.	Jack	DWG NO. XY-TF-021B-H265	
.XX±0.2	.X.*±	PROJ.	Can	CUSTOMER DRAWING	
.XXX±0.1	.XX.*±	SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A