







RoHS
Compliant

结构图面

REV	DESCRIPTION	APPR	CHECK	DRAW	DATE
△	新版发行		JACK	Yang	220811



P. C. B LAYOUT
TOLERANCE: ± 0.05



备注:

- 额定电流: 5.0A (单PIN);
- 额定电压: AC/DC 30V Max
- 绝缘耐压: AC 1000V 1 MINUTE, 无损伤
- 绝缘电阻: DC 500V 1 MINUTE, 1000M Ω Min
- 操作温度: -40° to +85°
- 塑胶材质: LCP/PA9T黑色/耐高温260° $\pm 5^\circ$,
- 五金材质: 黄铜(T=0.6mm)/镀半金锡1u"

Table:

PART NUMBER	P / N	Dim. A	Dim. B	Dim. C
JME2Mxx-H100001TZ-B	03pin	6.50	5.90	4.00
JME2Mxx-H100001TZ-B	04pin	8.50	7.90	6.00
JME2Mxx-H100001TZ-B	05pin	10.50	9.90	8.00
JME2Mxx-H100001TZ-B	06pin	12.50	11.90	10.00
JME2Mxx-H100001TZ-B	07pin	14.50	13.90	12.00
JME2Mxx-H100001TZ-B	08pin	16.50	15.90	14.00

QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)				SCALE: 1:1		NUMBER:		东莞市文章济美电子有限公司					
▽⁰ ▽^C⁰			MM		INCH	MATERIAL:		HRC:							
		. X ± 0.25		. X Ⓢ		DRAWN BY _____ DATE _____				TITLE: Battery 2.OPH 10.OH SMT 有柱 公座					
		. XX ± 0.15		. XX Ⓢ		JK-YANG									
		. XXX ± 0.05		. XXX Ⓢ											
		ANGULAR ±1°						CHECKED BY _____ DATE _____		 THIRD ANGLE PROJECTION		REVISE ON CAD ONLY			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						APPROVED BY _____ DATE _____		PART NO. JME2Mxx-H100001TZ-B				DWG NO. _____		SHEET NO. 1/1	

A4