

1.Description

This N-Channel MOSFET is produced using process that has been especially tailored to minimize the on-state resistance and yet maintain superior switching performance.


3.Application

- Inverter
- Synchronous rectifier

4.Pinning information

Pin	Symbol	Description
1	G	GATE
2	D	DRAIN
3	S	SOURCE

TO-252(DPAK)
top view



5.Absolute Maximum Ratings $T_c = 25^\circ\text{C}$

Parameter	Symbol	Rating	Units
Drain to Source Voltage	V_{DS}	60	V
Gate to Source Voltage	V_{GS}	± 20	
Drain Current -Continuous $T_c=25^\circ\text{C}$	I_D	50	A
-Continuous $T_A=25^\circ\text{C}$ (Note 1a)		11.5	
-Pulsed		100	
Single Pulse Avalanche Energy (Note 3)	E_{AS}	253	mJ
Power Dissipation $T_c=25^\circ\text{C}$	P_D	69	W
Power Dissipation $T_A=25^\circ\text{C}$ (Note 1a)		3.1	
Operating and Storage Junction Temperature Range	T_J, T_{STG}	-55 to 150	$^\circ\text{C}$



6.Thermal Characteristics

Parameter	Symbol	Rating	Units
Thermal Resistance, Junction to Case	$R_{\theta JC}$	1.8	°C/W
Thermal Resistance, Junction to Ambient (Note 1a)	$R_{\theta JA}$	40	°C/W



7. Electrical Characteristic (T_J=25°C unless otherwise noted)


Parameter	Symbol	Conditions	Min	Typ	Max	Units
Drain-Source Breakdown Voltage	BV _{DSS}	I _D =250μA, V _{GS} =0V	60			V
Breakdown Voltage Temperature Coefficient	$\frac{\Delta BV_{DSS}}{\Delta T_J}$	I _D =250μA Referenced to 25°C		77		mV/°C
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =48V, V _{GS} =0V			1	μA
Gate to Source Leakage Current	I _{GSS}	V _{GS} =±20V, V _{DS} =0V			±100	nA
Gate to Source Threshold Voltage	V _{GS(th)}	V _{DS} =V _{GS} , I _D =250μA	1	1.6	2.5	V
Gate to Source Threshold Voltage Temperature Coefficient	$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	I _D =250μA Referenced to 25°C		-8		mV/°C
Static Drain to Source On Resistance	R _{DS(on)}	V _{GS} =10V, I _D =10.7A		10	12.3	mΩ
		V _{GS} =4.5V, I _D =9.5A		12	15.4	mΩ
Forward Transconductance	g _{FS}	V _{DD} =5V, I _D =10.7A		41		S
Input Capacitance	C _{iss}	V _{DS} =30V, V _{GS} =0V f=1MHz		2420	3215	pF
Output Capacitance	C _{oss}			215	285	pF
Reverse Transfer Capacitance	C _{rss}			120	180	pF
Gate Resistance	R _g	f=1MHz		1.7		Ω
Turn-On DelayTime	t _{D(on)}	V _{DD} =30V, I _D =10.7A V _{GS} =10V, R _{GEN} =6Ω		11	20	ns
Rise Time	t _r			6	11	ns
Turn-Off DelayTime	t _{D(off)}			36	58	ns
Fall Time	t _f			4	10	ns
Total Gate Charge	Q _g	V _{GS} =0V to 10V, V _{DD} =30V V _{GS} =0V to 4.5V, I _D =10.7A		46	65	nC
Total Gate Charge	Q _g			23	32	nC
Gate to Source Gate Charge	Q _{gs}			7		nC
Gate to Drain "Miller" Charge	Q _{gd}			9		nC
Source to Drain Diode Forward Voltage	V _{SD}	V _{GS} =0V, I _S =10.7A (Note 2)		0.8	1.3	V
		V _{GS} =0V, I _S =2.6A (Note 2)		0.7	1.2	V
Reverse Recovery Time	t _{rr}	I _F =10.7A, di/dt=100A/μs		28	45	ns
Reverse Recovery Charge	Q _{rr}			21	34	nC



Notes:

1: $R_{\theta JA}$ is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins.

$R_{\theta JC}$ is guaranteed by design while $R_{\theta JA}$ is determined by the user's board design.



a) 40°C/W when mounted on a
1 in² pad of 2 oz copper



b) 96°C/W when mounted
on a minimum pad.

2: Pulse Test: Pulse Width < 300μs, Duty cycle < 2.0%.

3: E_{AS} of 253mJ is based on starting $T_J=25^{\circ}\text{C}$, $L=3\text{mH}$, $I_{AS}=13\text{A}$, $V_{DD}=60\text{V}$, $V_{GS}=10\text{V}$. 100% test at $L = 0.1\text{mH}$, $I_{AS}=41\text{A}$.



8.1 Typical characteristic




Figure 1: On-Region Characteristics




Figure 2: Normalized On-Resistance vs Drain Current and Gate Voltage




Figure 3: Normalized On Resistance vs Junction Temperature




Figure 4: On-Resistance Variation with Gate-to-Source Voltage




Figure 5: Transfer Characteristics




Figure 6: Source to Drain Diode Forward Voltage vs Source Current



8.2 Typical characteristic




Figure 7: Gate Charge Characteristics




Figure 8: Capacitance vs Drain to Source Voltage




Figure 9: Unclamped Inductive Switching Capability




Figure 10: Maximum Continuous Drain Current vs Case Temperature




Figure 11: Forward Bias Safe Operating Area





Figure 12: Single Pulse Maximum Power Dissipation




8.3Typical characteristic





9.TO-252 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	B	B1	B2	B3	B4	B5	B6	C	D
Min	5.1	6.4	5.6	9.5	5.9	1.35	0.4	0.1	0.85	4.35	2.15	2.286
Max	5.5	6.8	6.0	10.3	6.3	1.65	0.6	(typ.)	1.05	4.65	2.45	(typ.)

Symbol	D1	D2	D3	D4	D5	E	E1	R	R1	R2	R3
Min	0.66	0.81	0.65	0.42	0.42	0.86	0.05	0°	7°	7°	7°
Max	0.86	1.01	0.95	0.58	0.58	1.16	0.05	6°	(typ.)	(typ.)	(typ.)



10.Ordering information



yy: Year Code
ww: Week Code

Order Code	Package	Base QTY	Delivery Mode
UMW FDD5353	TO-252	2500	Tape and reel



11.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.