





P.C.B Layout



技术要求:

Technical requirement

一. 电气性能:

electrical performance

1-1. 额定电流: 3A AC DC.

rated current: 3A AC DC.

1-2. 接触电阻: $\leq 20\text{m}\Omega$

Contact resistance: $\leq 20\text{m}\Omega$

1-3. 绝缘电阻: $\geq 1000\text{M}\Omega$

Insulation resistance: $\geq 1000\text{M}\Omega$

1-4. 耐压: 550V AC/Minute

withstand voltage: 550V AC/Minute

二. 物理特性:

Physical characteristics

2-1.: 环境温度: $-55^{\circ}\text{C} \sim 105^{\circ}\text{C}$

environmental temperature: $-55^{\circ}\text{C} \sim 105^{\circ}\text{C}$

2-2. 焊接温度: $+260^{\circ}\text{C}$, 10s max

welding temperature: $+260^{\circ}\text{C}$, 10s max

三. 材质:

Material

3-1. 塑胶: PA6T(Black) UL94V-0

plastic: PA6T(Black) UL94V-0

3-2. 插针: 黄铜

contact pin: Brass/Gold plated

注: n为产品总PIN位数

图号 DOCUMENT NUMBER				NJ2.0-2xNA			
料号 MATERIALS NUMBER							
制图 DRAWER		Yang		Scale 比例		1:1	
审查 EXAMINE		Sun		Unit 单位		MM	
日期 DATE		2025.12.5		视角 THIRD ANGLE PROJECTION			