


## 1.Description

This N-Channel MOSFET has been designed specifically to improve the overall efficiency of DC/DC converters using either synchronous or conventional switching PWM controllers. It has been optimized for low gate charge, low  $R_{DS(ON)}$  and fast switching speed.

## 3.Pinning information

| Pin | Symbol | Description |
|-----|--------|-------------|
| 1   | G      | GATE        |
| 2   | D      | DRAIN       |
| 3   | S      | SOURCE      |

TO-252(DPAK)  
top view



## 4.Absolute Maximum Ratings $T_c = 25^\circ\text{C}$

| Parameter   | Symbol         | Rating     | Units              |
|---|----------------|------------|--------------------|
| Drain to Source Voltage   | $V_{DSS}$      | 30         | V                  |
| Gate to Source Voltage  | $V_{GS}$       | $\pm 20$   | V                  |
| Drain Current Continuous ( $T_c=25^\circ\text{C}$ , $V_{GS}=10\text{V}$ ) (Note 1)                        | $I_D$          | 160        | A                  |
| Continuous ( $T_c=25^\circ\text{C}$ , $V_{GS}=4.5\text{V}$ ) (Note 1)                                     |                | 150        | A                  |
| Continuous ( $T_{amb}=25^\circ\text{C}$ , $V_{GS}=10\text{V}$ , with $R_{\theta JA}=52^\circ\text{C/W}$ ) |                | 21         | A                  |
| Pulsed  |                | Figure 4   | A                  |
| Single Pulse Avalanche Energy (Note 2)  | $E_{AS}$       | 690        | mJ                 |
| Power Dissipation   | $P_D$          | 160        | W                  |
| Derate above $25^\circ\text{C}$   |                | 1.07       | $^\circ\text{C/W}$ |
| Storage Temperature   | $T_J, T_{STG}$ | -55 to 175 | $^\circ\text{C}$   |



5.Thermal Characteristics

| Parameter   | Symbol           | Rating | Units |
|---|------------------|--------|-------|
| Thermal Resistance, Junction-to-Case TO-252,TO-251                              | R <sub>θJC</sub> | 0.94   | °C/W  |
| Thermal Resistance, Junction-to-Ambient TO-252,TO-251                           | R <sub>θJA</sub> | 100    | °C/W  |
| Thermal Resistance, Junction-to-Ambient TO-252,1in <sup>2</sup> copper pad area | R <sub>θJA</sub> | 52     | °C/W  |



## 6. Electrical Characteristic (T<sub>c</sub>=25°C unless otherwise noted)

| Parameter                         | Symbol              | Conditions   |                       | Min | Typ  | Max  | Units |
|-----------------------------------|---------------------|--|-----------------------|-----|------|------|-------|
| Off Characteristics               |                     |  |                       |     |      |      |       |
| Drain to Source Breakdown Voltage | BV <sub>DSS</sub>   | I <sub>D</sub> =250μA, V <sub>GS</sub> =0V   |                       | 30  |      |      | V     |
| Zero Gate Voltage Drain Current   | I <sub>DSS</sub>    | V <sub>DS</sub> =24V   |                       |     |      | 1    | μA    |
|                                   |                     | V <sub>GS</sub> =0V  | T <sub>J</sub> =150°C |     |      | 250  | μA    |
| Gate to Source Leakage Current    | I <sub>GSS</sub>    | V <sub>GS</sub> =±20V  |                       |     |      | ±100 | nA    |
| On Characteristics                |                     |  |                       |     |      |      |       |
| Gate to Source Threshold Voltage  | V <sub>GS(th)</sub> | V <sub>DS</sub> =V <sub>GS</sub> , I <sub>D</sub> =250μA                                 |                       | 1   | 1.7  | 2.5  | V     |
| Drain to Source On Resistance     | R <sub>DS(ON)</sub> | I <sub>D</sub> =35A, V <sub>GS</sub> =10V  |                       |     | 3.2  | 3.9  | mΩ    |
|                                   |                     | I <sub>D</sub> =35A, V <sub>GS</sub> =4.5V   |                       |     | 3.6  | 4.4  | mΩ    |
| Dynamic Characteristics           |                     |  |                       |     |      |      |       |
| Input Capacitance                 | C <sub>iss</sub>    | V <sub>DS</sub> =15V, V <sub>GS</sub> =0V, f=1MHz  |                       |     | 5160 |      | pF    |
| Output Capacitance                | C <sub>oss</sub>    |  |                       |     | 990  |      | pF    |
| Reverse Transfer Capacitance      | C <sub>rss</sub>    |  |                       |     | 590  |      | pF    |
| Gate Resistance                   | R <sub>g</sub>      | V <sub>GS</sub> =0.5V, f=1MHz  |                       |     | 2.1  |      | Ω     |
| Total Gate Charge at 10V          | Q <sub>g(TOT)</sub> | V <sub>GS</sub> =0V to 10V   | V <sub>DD</sub> =15V  |     | 91   | 118  | nC    |
| Total Gate Charge at 5V           | Q <sub>g(5)</sub>   | V <sub>GS</sub> =0V to 5V  | I <sub>D</sub> =35A   |     | 48   | 62   | nC    |
| Threshold Gate Charge             | Q <sub>g(TH)</sub>  | V <sub>GS</sub> =0V to 1V  | I <sub>g</sub> =1mA   |     | 5    | 6.5  | nC    |
| Gate to Source Gate Charge        | Q <sub>gs</sub>     |  |                       |     | 14   |      | nC    |
| Gate Charge Threshold to Plateau  | Q <sub>gs2</sub>    |  |                       |     | 9    |      | nC    |
| Gate to Drain “Miller” Charge     | Q <sub>gd</sub>     |  |                       |     | 18   |      | nC    |
| Turn-On Time                      | t <sub>(on)</sub>   | V <sub>DD</sub> =15V, I <sub>D</sub> =35A<br>V <sub>GS</sub> =10V, R <sub>GS</sub> =3.3Ω |                       |     |      | 139  | ns    |
| Turn-On Delay Time                | t <sub>D(on)</sub>  |  |                       |     | 9    |      | ns    |
| Rise Time                         | t <sub>r</sub>      |  |                       |     | 83   |      | ns    |
| Turn-Off DelayTime                | t <sub>D(off)</sub> |  |                       |     | 83   |      | ns    |
| Fall Time                         | t <sub>f</sub>      |  |                       |     | 42   |      | ns    |
| Turn-Off Time                     | t <sub>off</sub>    |  |                       |     |      | 189  | ns    |




| Drain–Source Diode Characteristics    |          |                             |  |  |      |    |
|---------------------------------------|----------|-----------------------------|--|--|------|----|
| Source to Drain Diode Forward Voltage | $V_{SD}$ | $I_{SD}=35A$                |  |  | 1.25 | V  |
|                                       |          | $I_{SD}=15A$                |  |  | 1    | V  |
| Reverse Recovery Time                 | $t_{rr}$ | $I_F=35A, di/dt=100A/\mu s$ |  |  | 37   | ns |
| Reverse Recovery Charge               | $Q_{rr}$ | $I_F=35A, di/dt=100A/\mu s$ |  |  | 21   | nC |

Notes:

1: Package current limitation is 35A.



7.1Typical characteristic





## 7.2 Typical characteristic




Figure 5: Forward Bias Safe Operating Area




Figure 6: Unclamped Inductive Switching Capability




Figure 7: Transfer Characteristics




Figure 8: Saturation Characteristics




Figure 9: Drain to Source On Resistance vs Gate Voltage and Drain Current








Figure 10: Normalized Drain to Source On Resistance vs Junction Temperature



7.3Typical characteristic

|   |   |
|---|---|
|  <p>Figure 11: Normalized Gate Threshold Voltage vs Junction Temperature</p> |  <p>Figure 12: Normalized Drain to Source Breakdown Voltage vs Junction Temperature</p> |
|  <p>Figure 13: Capacitance vs Drain to Source Voltage</p>                  |  <p>Figure 14: Gate Charge Waveforms for Constant Gate Current</p>                    |



## 7.4 Typical characteristic




Figure 15. Unclamped Energy Test Circuit




Figure 16. Unclamped Energy Waveforms




Figure 17. Gate Charge Test Circuit




Figure 18. Gate Charge Waveforms




Figure 19. Switching Time Test Circuit





Figure 20. Switching Time Waveforms





## 7.5 Typical characteristic



### Notes:

The maximum rated junction temperature,  $T_{JM}$ , and the thermal resistance of the heat dissipating path determines the maximum allowable device power dissipation,  $P_{DM}$ , in an application. Therefore the application's ambient temperature,  $T_A(^{\circ}\text{C})$ , and thermal resistance  $R_{\theta JA}(^{\circ}\text{C/W})$  must be reviewed to ensure that  $T_{JM}$  is never exceeded. Equation 1 mathematically represents the relationship and serves as the basis for establishing the rating of the part.

$$P_{DM} = \frac{(T_{JM} - T_A)}{R_{\theta JA}} \quad (\text{EQ. 1})$$

In using surface mount devices such as the TO-252 package, the environment in which it is applied will have a significant influence on the part's current and maximum power dissipation ratings. Precise determination of PDM is complex and influenced by many factors:

1. Mounting pad area onto which the device is attached and whether there is copper on one side or both sides of the board.
2. The number of copper layers and the thickness of the board.
3. The use of external heat sinks.
4. The use of thermal vias.
5. Air flow and board orientation.
6. For non steady state applications, the pulse width, the duty cycle and the transient thermal response of the part, the board and the environment they are in.



Figure 21 defines the  $R_{\theta JA}$  for the device as a function of the top copper (component side) area. This is for a horizontally positioned FR-4 board with 1oz copper after 1000 seconds of steady state power with no air flow. This graph provides the necessary information for calculation of the steady state junction temperature or power dissipation. Pulse applications can be evaluated using the Fairchild device Spice thermal model or manually utilizing the normalized maximum transient thermal impedance curve.

Thermal resistances corresponding to other copper areas can be obtained from Figure 21 or by calculation using Equation 2 or 3. Equation 2 is used for copper area defined in inches square and equation 3 is for area in centimeters square. The area, in square inches or square centimeters is the top copper area including the gate and source pads.


$$R_{\theta JA} = 33.32 + \frac{23.84}{(0.268 + \text{Area})} \quad (\text{EQ. 2})$$

$$R_{\theta JA} = 33.32 + \frac{154}{(1.73 + \text{Area})} \quad (\text{EQ. 3})$$

Area in Centimeters Squared



8.TO-252 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

| Symbol | A1   | A2   | A3   | b    | c    | D    | D1   | D2   | E     | E1   | E2   | e     | L1   | L2   | L3   | θ    |
|--------|------|------|------|------|------|------|------|------|-------|------|------|-------|------|------|------|------|
| Min    | 0.00 | 2.18 | 0.90 | 0.65 | 0.46 | 6.35 | 4.95 | 4.32 | 9.40  | 5.97 | 5.21 | 2.286 | 0.89 | 1.70 | 0.60 | 0.00 |
| Max    | 0.13 | 2.39 | 1.10 | 0.85 | 0.61 | 6.73 | 5.46 | 4.90 | 10.41 | 6.22 | 5.38 |       | BSC  | 1.27 | 1.90 | 1.00 |



9.Ordering information



yy: Year Code  
ww: Week Code

| Order Code  | Package | Base QTY | Delivery Mode |
|-------------|---------|----------|---------------|
| UMW FDD8870 | TO-252  | 2500     | Tape and reel |



## 10.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.