


1.Features

- Audio Frequency General Purpose Amplifier Applications
- 2SC2712 TRANSISTOR (NPN)
- Low Noise: NF=1dB (Typ), 10dB(MAX)
- Complementary to 2SA1162

2.Pinning Information

Pin	Symbol	Description
1	B	BASE
2	E	EMITTER
3	C	COLLECTOR

SOT-23



3.Absolute Maximum Ratings $T_A= 25^{\circ}\text{C}$

Parameter	Symbol	Value	Units
Collector-Base Voltage	V_{CBO}	60	V
Collector-Emitter Voltage	V_{CEO}	50	V
Emitter-Base Voltage	V_{EBO}	5	V
Collector Current -Continuous	I_C	150	mA
Collector Power Dissipation	P_C	150	mW
Junction Temperature	T_J	150	$^{\circ}\text{C}$
Storage Temperature	T_{STG}	-55 to 150	$^{\circ}\text{C}$



4. Electrical Characteristics $T_A = 25^\circ\text{C}$

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Collector-base breakdown voltage	$V_{(BR)CBO}$	$I_C=100\mu\text{A}, I_E=0$	60			V
Collector-emitter breakdown voltage	$V_{(BR)CEO}$	$I_C=1\text{mA}, I_B=0$	50			V
Emitter-base breakdown voltage	$V_{(BR)EBO}$	$I_E=100\mu\text{A}, I_C=0$	5			V
Collector cut-off current	I_{CBO}	$V_{CB}=60\text{V}, I_E=0$			0.1	μA
Emitter cut-off current	I_{EBO}	$V_{EB}=5\text{V}, I_C=0$			0.1	μA
DC current gain	h_{FE}	$V_{CE}=6\text{V}, I_C=2\text{mA}$	70		700	
Collector-emitter saturation voltage	$V_{CE(sat)}$	$I_C=100\text{mA}, I_B=10\text{mA}$		0.1	0.25	V
Transition frequency	f_T	$V_{CE}=10\text{V}, I_C=1\text{mA}$	80			MHz
Output capacitance	C_{ob}	$V_{CB}=10\text{V}, I_E=0, f=1\text{MHz}$		2	3.5	pf
Noise Figure	N_F	$V_{CE}=6\text{V}, I_C=0.1\text{mA}$ $R_g=10\text{k}\Omega, f=1\text{kHz}$		1	10	dB

5. Classification of h_{FE}

Rank	O	Y	GR	BL
Range	70-140	120-240	200-400	350-700
Marking	LO	LY	LG	LL




6.1 Typical Characteristics

<p style="text-align: center;">I_C, Collector Current (mA)</p> <p style="text-align: center;">V_{CE}, Collector-emitter Voltage (V)</p>	<p style="text-align: center;">h_{FE}, DC Current Gain</p> <p style="text-align: center;">I_C, Collector Current (mA)</p>
<p style="text-align: center;">Figure 1: Static Characteristic</p>	<p style="text-align: center;">Figure 2: h_{FE} — I_C</p>
<p style="text-align: center;">V_{CEsat}, Collector-emitter Saturation Voltage (mV)</p> <p style="text-align: center;">I_C, Collector Current (mA)</p>	<p style="text-align: center;">V_{BEsat}, Base-emitter Saturation Voltage (mV)</p> <p style="text-align: center;">I_C, Collector Current (mA)</p>
<p style="text-align: center;">Figure 3: V_{CEsat} — I_C</p>	<p style="text-align: center;">Figure 4: V_{BEsat} — I_C</p>
<p style="text-align: center;">I_C, Collector Current (mA)</p> <p style="text-align: center;">V_{BE}, Base-emitter Voltage (mV)</p>	<p style="text-align: center;">f_T, Transition Frequency (MHz)</p> <p style="text-align: center;">I_C, Collector Current (mA)</p>
<p style="text-align: center;">Figure 5: I_C — V_{BE}</p>	<p style="text-align: center;">Figure 6: f_T — I_C</p>




6.2 Typical Characteristics





7.SOT-23 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	B	b _p	C	D	E	H _E	A1	L _p
Min	0.95	1.78	0.35	0.08	2.70	1.20	2.20	0.013	0.20
Max	1.40	2.04	0.50	0.19	3.10	1.65	3.00	0.100	0.50



8. Ordering information



Order Code	Package	Base QTY	Delivery Mode
UMW 2SC2712	SOT-23	3000	Tape and reel



9.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.