








修订 REV	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
A0		NEW DWG		

TO MAKE SURE THE CAP CAN
BE PUT ON THE MIDPOINT
FOR 04P TO 15P

CAP
(FOR PICK AND PLACE
SYSTEMS)



SEC:A-A



P.C.B LAYOUT

- (1)Temperature: -25℃~85℃
(2)Relative humidity: ≤85% RH
(3)Rating: AC/DC 150V 1A
(4)Contact Resistance:≤30m ohm
(5)Insulation Resistance:≥500M ohm
(6)Withstand Voltage: AC 500V for 1min
(7)Soldering Temperature: 260±5℃ 5±0.5s



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表				TITLE: 产品名称: DF13 1.25间距单排立贴针座	
X.X ±0.30	X.X' ±3°	APPD: 核准: 谢亮		PART NO: 产品编号: HDGC1252WV-S-6P	
X.XX ±0.30	X.XX' ±2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT
X.XXX ±0.10	X.XXX' ±1°	DRAW: 绘图: 黄艳兰		1:1	mm
					A001