


REV.	DESCRIPTION	ECN NO.	NAME	DATE





-, MATERIAL:

1. Insulator: PBT+30%Glass Fiber
2. Contact: Brass
3. Contact Plated: Gold Flash over Tin Or
Glod Plated Or Tin Plated
4. Shell: Steel, Nickel Plated

2. SPECIFICATION:


- 1.Current Rating:5 AMPS
- 2.Insulation Resistance: 100M Ω MIN. At 500VDC
- 3.Dielectric Strength: 500V for One minute
- 4.Operation Temperature: -55° C~+105° C.

※【胶芯颜色、防火要求、环保要求及电镀规格 依据客户实际订单要求为准】



RECOMMEND PCB LAYOUT (T=1.6)

PCB TOLERANCE:±0.05

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				BXCONN [®]	
DIM. x. ±0.30 x.x ±0.25 x.xx ±0.15 GENERAL ANGLE: x° ±5.0° x.x° ±2.0° x.xx° ±1.0°		TITLE: HDR15F 铆锁					
DWG. NO.: D-USB-DS1038-15M				CHECKED: MAX			
PART NO.: D-USB-DS1038-15M				DRAWN: ELLA			
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL