












	A	B	C	D	E																										
			REV.	DESCRIPTION	ECN NO.	NAME	DATE																								
1		 适用线路板 (PCB LAYOUT)																													
2																															
3				SECTION A-A																											
4																															
5	技术指标 (Technical Index):	<ol style="list-style-type: none"> 温度范围 (Temperature range): $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$. 额定电压 (Rated voltage): 100V, AC. 额定电流 (Rated current): 1.0A AC, DC. 接触电阻 (Contact resistance): $\leq 20\text{m}\Omega$. 绝缘电阻 (Insulation resistance): $\geq 500\text{M}\Omega$. 耐压值 (Withstanding voltage): 500V AC/minute. 	<table border="1"> <thead> <tr> <th>GENERAL TOLERANCE</th> <th colspan="3">DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD</th> <th>BXCONN®</th> </tr> </thead> <tbody> <tr> <td>DIM. x x.x x.xx TOL. ±0.50 ±0.20 ±0.10 GENERAL ANGLE: x.* ±1°</td> <td colspan="3">TITLE: ZH1.5直针 WTB</td> <td rowspan="4">  </td> </tr> <tr> <td></td> <td colspan="3">DWG. NO.: WF-ZH1.5-XPA1</td> <td>CHECKED: MAX</td> </tr> <tr> <td></td> <td colspan="3">PART NO.: WF-ZH1.5-XPA1</td> <td>DRAWN: ELLA</td> </tr> <tr> <td>UNIT: mm</td> <td>SCALE: none</td> <td>SHEET: 1 of 1</td> <td>DWG. SIZE: A4</td> <td>APPROVED: WILL</td> </tr> </tbody> </table>	GENERAL TOLERANCE	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD			BXCONN®	DIM. x x.x x.xx TOL. ±0.50 ±0.20 ±0.10 GENERAL ANGLE: x.* ±1°	TITLE: ZH1.5直针 WTB					DWG. NO.: WF-ZH1.5-XPA1			CHECKED: MAX		PART NO.: WF-ZH1.5-XPA1			DRAWN: ELLA	UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	APPROVED: WILL			
GENERAL TOLERANCE	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD			BXCONN®																											
DIM. x x.x x.xx TOL. ±0.50 ±0.20 ±0.10 GENERAL ANGLE: x.* ±1°	TITLE: ZH1.5直针 WTB																														
	DWG. NO.: WF-ZH1.5-XPA1				CHECKED: MAX																										
	PART NO.: WF-ZH1.5-XPA1				DRAWN: ELLA																										
UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4		APPROVED: WILL																										

A	B	C	D	E																																																																																																					
   <table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th>CKT (1.5mm pitch)</th> <th>W</th> <th>PCS/RELL</th> <th>RELL/CARTON</th> <th>SUM(PCS)</th> </tr> </thead> <tbody> <tr> <td>2</td> <td rowspan="12" style="vertical-align: middle; text-align: center;">16</td> <td rowspan="12" style="vertical-align: middle; text-align: center;">900</td> <td rowspan="12" style="vertical-align: middle; text-align: center;">14</td> <td rowspan="12" style="vertical-align: middle; text-align: center;">12600</td> </tr> <tr> <td>3</td> </tr> <tr> <td>4</td> </tr> <tr> <td>5</td> </tr> <tr> <td>6</td> </tr> <tr> <td>7</td> </tr> <tr> <td>8</td> </tr> <tr> <td>9</td> </tr> <tr> <td>10</td> </tr> <tr> <td>11</td> </tr> <tr> <td>12</td> </tr> <tr> <td>13</td> </tr> <tr> <td>14</td> <td rowspan="7" style="vertical-align: middle; text-align: center;">32</td> <td rowspan="7" style="vertical-align: middle; text-align: center;">900</td> <td rowspan="7" style="vertical-align: middle; text-align: center;">8</td> <td rowspan="7" style="vertical-align: middle; text-align: center;">7200</td> </tr> <tr> <td>15</td> </tr> <tr> <td>16</td> </tr> <tr> <td>17</td> </tr> <tr> <td>18</td> </tr> <tr> <td>19</td> </tr> <tr> <td>20</td> </tr> <tr> <td>14</td> <td rowspan="7" style="vertical-align: middle; text-align: center;">44</td> <td rowspan="7" style="vertical-align: middle; text-align: center;">900</td> <td rowspan="7" style="vertical-align: middle; text-align: center;">6</td> <td rowspan="7" style="vertical-align: middle; text-align: center;">5400</td> </tr> <tr> <td>15</td> </tr> <tr> <td>16</td> </tr> <tr> <td>17</td> </tr> <tr> <td>18</td> </tr> <tr> <td>19</td> </tr> <tr> <td>20</td> </tr> </tbody> </table>	CKT (1.5mm pitch)	W	PCS/RELL	RELL/CARTON	SUM(PCS)	2	16	900	14	12600	3	4	5	6	7	8	9	10	11	12	13	14	32	900	8	7200	15	16	17	18	19	20	14	44	900	6	5400	15	16	17	18	19	20	 <table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th>纸箱型号 Carton Type</th> <th>小型 Small Size</th> <th>中型 Medium</th> <th>标准型 Standard</th> </tr> </thead> <tbody> <tr> <td>高度 Height (CM)</td> <td>7.5</td> <td>15</td> <td>32</td> </tr> </tbody> </table> 	纸箱型号 Carton Type	小型 Small Size	中型 Medium	标准型 Standard	高度 Height (CM)	7.5	15	32	 <table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th>CKT (1.5mm pitch)</th> <th>B0</th> <th>W</th> <th>F</th> <th>S</th> </tr> </thead> <tbody> <tr> <td>2</td> <td>4.80</td> <td rowspan="12" style="vertical-align: middle; text-align: center;">16</td> <td rowspan="12" style="vertical-align: middle; text-align: center;">7.50</td> <td rowspan="12" style="vertical-align: middle; text-align: center;">24</td> </tr> <tr> <td>3</td> <td>6.30</td> </tr> <tr> <td>4</td> <td>7.80</td> </tr> <tr> <td>5</td> <td>9.30</td> </tr> <tr> <td>6</td> <td>10.80</td> </tr> <tr> <td>7</td> <td>12.30</td> </tr> <tr> <td>8</td> <td>13.80</td> </tr> <tr> <td>9</td> <td>15.30</td> </tr> <tr> <td>10</td> <td>16.80</td> </tr> <tr> <td>11</td> <td>18.30</td> </tr> <tr> <td>12</td> <td>19.80</td> </tr> <tr> <td>13</td> <td>21.30</td> </tr> <tr> <td>14</td> <td>22.80</td> <td rowspan="8" style="vertical-align: middle; text-align: center;">32</td> <td rowspan="8" style="vertical-align: middle; text-align: center;">14.20±0.10</td> <td rowspan="8" style="vertical-align: middle; text-align: center;">32</td> </tr> <tr> <td>15</td> <td>24.30</td> </tr> <tr> <td>16</td> <td>25.80</td> </tr> <tr> <td>17</td> <td>27.30</td> </tr> <tr> <td>18</td> <td>28.80</td> </tr> <tr> <td>19</td> <td>30.30</td> </tr> <tr> <td>20</td> <td>31.80</td> </tr> <tr> <td>14</td> <td>20.20±0.10</td> </tr> </tbody> </table>	CKT (1.5mm pitch)	B0	W	F	S	2	4.80	16	7.50	24	3	6.30	4	7.80	5	9.30	6	10.80	7	12.30	8	13.80	9	15.30	10	16.80	11	18.30	12	19.80	13	21.30	14	22.80	32	14.20±0.10	32	15	24.30	16	25.80	17	27.30	18	28.80	19	30.30	20	31.80	14	20.20±0.10	<p>NOTE(注):</p> <p>1.10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE $\pm 0.2\text{mm}$. (10片孔距累积公差$\pm 0.2\text{mm}$.)</p> <p>2. CARRIER CAMBER NOT TO EXCEED 1mm IN 100mm. (载带拱/弧形 MAX:1/100mm.)</p> <p>3. ALL DIMENSIONS MEET EIA-481 REQUIREMENTS. (所有的尺寸要满足协会EIA-481规范.)</p> <p>4. MATERIAL: CLEAR ANTISTATIC PS, COLD SEALING. (载带材料:透明抗静电 PS,冷封.)</p> <p>5. THICKNESS: 0.50±0.05mm. (载带厚度:0.50±0.05mm.)</p> <p>6. PACKING LENGTH PER REEL: 7.68 METERS. (每卷包装长度:7.68米.)</p> <p>7. COMPONENT LOAD PER REEL: 900 PCS. (每卷包装数量:900只, 前后各空30只.)</p> <p>8. 纸箱分小、中、标准型3种规格型号:装箱为整箱(左下包装量)采用标准型纸箱包装,未达到整箱数量以产品量适当采用小型或中型纸箱包装.</p>
	CKT (1.5mm pitch)	W	PCS/RELL	RELL/CARTON	SUM(PCS)																																																																																																				
	2	16	900	14	12600																																																																																																				
	3																																																																																																								
	4																																																																																																								
	5																																																																																																								
	6																																																																																																								
	7																																																																																																								
	8																																																																																																								
	9																																																																																																								
	10																																																																																																								
	11																																																																																																								
	12																																																																																																								
	13																																																																																																								
	14	32	900	8	7200																																																																																																				
	15																																																																																																								
	16																																																																																																								
	17																																																																																																								
	18																																																																																																								
	19																																																																																																								
20																																																																																																									
14	44	900	6	5400																																																																																																					
15																																																																																																									
16																																																																																																									
17																																																																																																									
18																																																																																																									
19																																																																																																									
20																																																																																																									
纸箱型号 Carton Type	小型 Small Size	中型 Medium	标准型 Standard																																																																																																						
高度 Height (CM)	7.5	15	32																																																																																																						
CKT (1.5mm pitch)	B0	W	F	S																																																																																																					
2	4.80	16	7.50	24																																																																																																					
3	6.30																																																																																																								
4	7.80																																																																																																								
5	9.30																																																																																																								
6	10.80																																																																																																								
7	12.30																																																																																																								
8	13.80																																																																																																								
9	15.30																																																																																																								
10	16.80																																																																																																								
11	18.30																																																																																																								
12	19.80																																																																																																								
13	21.30																																																																																																								
14	22.80	32	14.20±0.10	32																																																																																																					
15	24.30																																																																																																								
16	25.80																																																																																																								
17	27.30																																																																																																								
18	28.80																																																																																																								
19	30.30																																																																																																								
20	31.80																																																																																																								
14	20.20±0.10																																																																																																								
REV.	DESCRIPTION			ECN NO.	NAME	DATE																																																																																																			

WWW.BXCONN.COM 东莞市宝讯精密技术有限公司 ARTICLE: BX-CN-001-A