






修订 REV	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
A0		NEW DWG		



A VIEW




P.C.B LAYOUT



- (1)Temperature: -25℃~85℃
- (2)Relative humidity: ≤85% RH
- (3)Rating: DC 30V 1A
- (4)Contact Resistance:≤100m ohm
- (5)Insulation Resistance:≥100M ohm
- (6)Withstand Voltage: AC 500V for 1min
- (7)Soldering Temperature: 260±5℃ 5±0.5s



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表				TITLE: 产品名称: DF11 2.0间距双排立贴针座					
X.X	±0.30	X.X*	±3°	APPD: 核准: 谢亮		PART NO: 产品编号: HDGC2009WV-S-2x6P			
X.XX	±0.30	X.XX*	±2°	CHECK: 校对: 王建业		DATE	SCALE	UNIT	CODE NUMBER
X.XXX	±0.10	X.XXX*	±1°	DRAW: 绘图: 黄艳兰			1:1	mm	A001

1
2
3
4
5
6
7
8