

	A	B	C	D	E																																																																																										
			REV.	DESCRIPTION	ECN NO.	NAME	DATE																																																																																								
1				<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <th style="width: 10%;">Part No</th> <th style="width: 10%;">CKT</th> <th style="width: 10%;">A</th> <th style="width: 10%;">B</th> </tr> <tr> <td>WF-PH2.0-2PB1</td> <td>2</td> <td>2.0</td> <td>6.0</td> </tr> <tr> <td>WF-PH2.0-3PB1</td> <td>3</td> <td>4.0</td> <td>8.0</td> </tr> <tr> <td>WF-PH2.0-4PB1</td> <td>4</td> <td>6.0</td> <td>10.0</td> </tr> <tr> <td>WF-PH2.0-5PB1</td> <td>5</td> <td>8.0</td> <td>12.0</td> </tr> <tr> <td>WF-PH2.0-6PB1</td> <td>6</td> <td>10.0</td> <td>14.0</td> </tr> <tr> <td>WF-PH2.0-7PB1</td> <td>7</td> <td>12.0</td> <td>16.0</td> </tr> <tr> <td>WF-PH2.0-8PB1</td> <td>8</td> <td>14.0</td> <td>18.0</td> </tr> <tr> <td>WF-PH2.0-9PB1</td> <td>9</td> <td>16.0</td> <td>20.0</td> </tr> <tr> <td>WF-PH2.0-10PB1</td> <td>10</td> <td>18.0</td> <td>22.0</td> </tr> <tr> <td>WF-PH2.0-11PB1</td> <td>11</td> <td>20.0</td> <td>24.0</td> </tr> <tr> <td>WF-PH2.0-12PB1</td> <td>12</td> <td>22.0</td> <td>26.0</td> </tr> <tr> <td>WF-PH2.0-13PB1</td> <td>13</td> <td>24.0</td> <td>28.0</td> </tr> <tr> <td>WF-PH2.0-14PB1</td> <td>14</td> <td>26.0</td> <td>30.0</td> </tr> <tr> <td>WF-PH2.0-15PB1</td> <td>15</td> <td>28.0</td> <td>32.0</td> </tr> <tr> <td>WF-PH2.0-16PB1</td> <td>16</td> <td>30.0</td> <td>34.0</td> </tr> <tr> <td>WF-PH2.0-17PB1</td> <td>17</td> <td>32.0</td> <td>36.0</td> </tr> <tr> <td>WF-PH2.0-18PB1</td> <td>18</td> <td>34.0</td> <td>38.0</td> </tr> <tr> <td>WF-PH2.0-19PB1</td> <td>19</td> <td>36.0</td> <td>40.0</td> </tr> <tr> <td>WF-PH2.0-20PB1</td> <td>20</td> <td>38.0</td> <td>42.0</td> </tr> </table>	Part No	CKT	A	B	WF-PH2.0-2PB1	2	2.0	6.0	WF-PH2.0-3PB1	3	4.0	8.0	WF-PH2.0-4PB1	4	6.0	10.0	WF-PH2.0-5PB1	5	8.0	12.0	WF-PH2.0-6PB1	6	10.0	14.0	WF-PH2.0-7PB1	7	12.0	16.0	WF-PH2.0-8PB1	8	14.0	18.0	WF-PH2.0-9PB1	9	16.0	20.0	WF-PH2.0-10PB1	10	18.0	22.0	WF-PH2.0-11PB1	11	20.0	24.0	WF-PH2.0-12PB1	12	22.0	26.0	WF-PH2.0-13PB1	13	24.0	28.0	WF-PH2.0-14PB1	14	26.0	30.0	WF-PH2.0-15PB1	15	28.0	32.0	WF-PH2.0-16PB1	16	30.0	34.0	WF-PH2.0-17PB1	17	32.0	36.0	WF-PH2.0-18PB1	18	34.0	38.0	WF-PH2.0-19PB1	19	36.0	40.0	WF-PH2.0-20PB1	20	38.0	42.0	<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <th style="width: 10%;">序号</th> <th style="width: 10%;">品名</th> <th style="width: 10%;">材质</th> </tr> <tr> <td>1</td> <td>PH2.0弯针WTB胶芯</td> <td>LCP UL94V-0 镀锡</td> </tr> <tr> <td>2</td> <td>PH2.0弯针WTB端子</td> <td>铜合金/表面镀锡</td> </tr> </table>	序号	品名	材质	1	PH2.0弯针WTB胶芯	LCP UL94V-0 镀锡	2	PH2.0弯针WTB端子	铜合金/表面镀锡	
Part No	CKT	A	B																																																																																												
WF-PH2.0-2PB1	2	2.0	6.0																																																																																												
WF-PH2.0-3PB1	3	4.0	8.0																																																																																												
WF-PH2.0-4PB1	4	6.0	10.0																																																																																												
WF-PH2.0-5PB1	5	8.0	12.0																																																																																												
WF-PH2.0-6PB1	6	10.0	14.0																																																																																												
WF-PH2.0-7PB1	7	12.0	16.0																																																																																												
WF-PH2.0-8PB1	8	14.0	18.0																																																																																												
WF-PH2.0-9PB1	9	16.0	20.0																																																																																												
WF-PH2.0-10PB1	10	18.0	22.0																																																																																												
WF-PH2.0-11PB1	11	20.0	24.0																																																																																												
WF-PH2.0-12PB1	12	22.0	26.0																																																																																												
WF-PH2.0-13PB1	13	24.0	28.0																																																																																												
WF-PH2.0-14PB1	14	26.0	30.0																																																																																												
WF-PH2.0-15PB1	15	28.0	32.0																																																																																												
WF-PH2.0-16PB1	16	30.0	34.0																																																																																												
WF-PH2.0-17PB1	17	32.0	36.0																																																																																												
WF-PH2.0-18PB1	18	34.0	38.0																																																																																												
WF-PH2.0-19PB1	19	36.0	40.0																																																																																												
WF-PH2.0-20PB1	20	38.0	42.0																																																																																												
序号	品名	材质																																																																																													
1	PH2.0弯针WTB胶芯	LCP UL94V-0 镀锡																																																																																													
2	PH2.0弯针WTB端子	铜合金/表面镀锡																																																																																													
2																																																																																															
3																																																																																															
4	5																																																																																														
技术指标 (Technical Index): <ol style="list-style-type: none"> 工作温度 (Temperature range): -40°C ~ 125°C. 额定电压 (Rated voltage): 200V DC/AC(rms). 额定电流 (Rated current): 2.0A. 接触电阻 (Contact resistance): ≤ 25mΩ. 耐压值 (Withstanding voltage): 500V AC/minute. 绝缘电阻 (Insulation resistance): ≥ 1000MΩ. 																																																																																															
5	<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td style="width: 10%;">GENERAL TOLERANCE</td> <td colspan="3" style="width: 90%;">DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD</td> </tr> <tr> <td style="text-align: center;"> DIM. x: ±0.50 x.x: ±0.20 x.xx: ±0.10 x...: ±0.10 </td> <td colspan="3" style="text-align: center;">TITLE: PH2.0弯针WTB</td> </tr> <tr> <td style="text-align: center;"> GENERAL ANGLE: x: ±1° </td> <td colspan="3" style="text-align: center;">DWG. NO.: WF-PH2.0-XPB1</td> </tr> <tr> <td></td> <td colspan="3" style="text-align: center;">DRAWN: ELLA</td> </tr> <tr> <td></td> <td colspan="3" style="text-align: center;">APPROVED: WILL</td> </tr> <tr> <td style="text-align: center;"> </td> <td style="text-align: center;">UNIT: mm</td> <td style="text-align: center;">SCALE: none</td> <td style="text-align: center;">SHEET: 1 of 1</td> </tr> <tr> <td></td> <td style="text-align: center;">DWG. SIZE: A4</td> <td style="text-align: center;">LAYER: bxconn</td> <td></td> </tr> </table>	GENERAL TOLERANCE	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD			DIM. x: ±0.50 x.x: ±0.20 x.xx: ±0.10 x...: ±0.10	TITLE: PH2.0弯针WTB			GENERAL ANGLE: x: ±1°	DWG. NO.: WF-PH2.0-XPB1				DRAWN: ELLA				APPROVED: WILL				UNIT: mm	SCALE: none	SHEET: 1 of 1		DWG. SIZE: A4	LAYER: bxconn																																																																			
GENERAL TOLERANCE	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD																																																																																														
DIM. x: ±0.50 x.x: ±0.20 x.xx: ±0.10 x...: ±0.10	TITLE: PH2.0弯针WTB																																																																																														
GENERAL ANGLE: x: ±1°	DWG. NO.: WF-PH2.0-XPB1																																																																																														
	DRAWN: ELLA																																																																																														
	APPROVED: WILL																																																																																														
	UNIT: mm	SCALE: none	SHEET: 1 of 1																																																																																												
	DWG. SIZE: A4	LAYER: bxconn																																																																																													

技术指标 (Technical Index):

1. 工作温度 (Temperature range): $-40^{\circ}\text{C} \sim 125^{\circ}\text{C}$.
2. 额定电压 (Rated voltage): 200V DC/AC(rms).
3. 额定电流 (Rated current): 2.0A.
4. 接触电阻 (Contact resistance): $\leq 25\text{m}\Omega$.
5. 耐压值 (Withstanding voltage): 500V AC/minute.
6. 绝缘电阻 (Insulation resistance): $\geq 1000\text{M}\Omega$.

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					BXCONN®
GENERAL ANGLE: x: $\pm 1^\circ$	DIM. TOL.	TITLE: PH2.0 针 WTB					
	x: ± 0.50						
	x.x: ± 0.20						
	x.xx: ± 0.10						
		DWG. NO.: WF-PH2.0-XPB1			CHECKED: MAX		
		PART NO.: WF-PH2.0-XPB1			DRAWN: ELLA		
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL
							

A		B		C		D		E																																																																																																																																				
REV.	DESCRIPTION				ECN NO.	NAME		DATE																																																																																																																																				
1				<p>NOTE(注):</p> <ol style="list-style-type: none"> 1.10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE $\pm 0.2\text{mm}$. (10片孔距累积公差$\pm 0.2\text{mm}$.) 2. CARRIER CAMBER NOT TO EXCEED 1mm IN 100mm. (载带拱/弧形MAX:1/100mm.) 3. ALL DIMENSIONS MEET EIA-481 REQUIREMENTS. (所有的尺寸要满足协会EIA-481规范.) 4. MATERIAL: CLEAR ANTISTATIC PS, COLD SEALING. (载带材料:透明抗静电PS,冷封.) 5. THICKNESS: 0.50±0.05mm. (载带厚度:0.50±0.05mm.) 6. PACKING LENGTH PER REEL: 7.008 METERS. (每卷包装长度:7.008米.) 7. COMPONENT LOAD PER REEL: 500 PCS. (每卷包装数量:500只, 每卷包装数量:550只, 前后各空17只.) 8. 纸箱装箱以不超过装箱线为准, 空余位置用塑料泡沫及保尼龙填充. 9. 纸箱分小、中、标准型3种规格型号: 装箱为整箱(左下包装量)采用标准型纸箱包装, 未达到整箱数量以产品量适当采用小型或中型纸箱包装. 																																																																																																																																								
2																																																																																																																																												
3					<table border="1"> <thead> <tr> <th>纸箱型号 Carton Type</th> <th>小型 Small Size</th> <th>中型 Medium</th> <th>标准型 Standard</th> </tr> </thead> <tbody> <tr> <td>高度 Height (CM)</td> <td>7.5</td> <td>15</td> <td>32</td> </tr> </tbody> </table>	纸箱型号 Carton Type	小型 Small Size	中型 Medium	标准型 Standard	高度 Height (CM)	7.5	15	32	<table border="1"> <thead> <tr> <th>CKT (2.0mm pitch)</th> <th>B0</th> <th>W</th> <th>F</th> <th>S</th> </tr> </thead> <tbody> <tr> <td>2</td> <td>6.30</td> <td>16</td> <td>7.50</td> <td></td> </tr> <tr> <td>3</td> <td>8.30</td> <td></td> <td></td> <td></td> </tr> <tr> <td>4</td> <td>10.30</td> <td></td> <td></td> <td></td> </tr> <tr> <td>5</td> <td>12.30</td> <td></td> <td></td> <td></td> </tr> <tr> <td>6</td> <td>14.30</td> <td></td> <td></td> <td></td> </tr> <tr> <td>7</td> <td>16.30</td> <td></td> <td></td> <td></td> </tr> <tr> <td>8</td> <td>18.30</td> <td>32</td> <td>14.20±0.10</td> <td>28.40</td> </tr> <tr> <td>9</td> <td>20.30</td> <td></td> <td></td> <td></td> </tr> <tr> <td>10</td> <td>22.30</td> <td></td> <td></td> <td></td> </tr> <tr> <td>11</td> <td>24.30</td> <td></td> <td></td> <td></td> </tr> <tr> <td>12</td> <td>26.30</td> <td>44</td> <td>20.20±0.10</td> <td>40.40</td> </tr> <tr> <td>13</td> <td>28.30</td> <td></td> <td></td> <td></td> </tr> <tr> <td>14</td> <td>30.30</td> <td></td> <td></td> <td></td> </tr> <tr> <td>15</td> <td>32.30</td> <td></td> <td></td> <td></td> </tr> <tr> <td>16</td> <td>34.30</td> <td></td> <td></td> <td></td> </tr> <tr> <td>17</td> <td>36.30</td> <td></td> <td></td> <td></td> </tr> <tr> <td>18</td> <td>38.30</td> <td>56</td> <td>26.20±0.10</td> <td>52.40</td> </tr> <tr> <td>19</td> <td>40.30</td> <td></td> <td></td> <td></td> </tr> <tr> <td>20</td> <td>42.30</td> <td></td> <td></td> <td></td> </tr> </tbody> </table>	CKT (2.0mm pitch)	B0	W	F	S	2	6.30	16	7.50		3	8.30				4	10.30				5	12.30				6	14.30				7	16.30				8	18.30	32	14.20±0.10	28.40	9	20.30				10	22.30				11	24.30				12	26.30	44	20.20±0.10	40.40	13	28.30				14	30.30				15	32.30				16	34.30				17	36.30				18	38.30	56	26.20±0.10	52.40	19	40.30				20	42.30																													
纸箱型号 Carton Type	小型 Small Size	中型 Medium	标准型 Standard																																																																																																																																									
高度 Height (CM)	7.5	15	32																																																																																																																																									
CKT (2.0mm pitch)	B0	W	F	S																																																																																																																																								
2	6.30	16	7.50																																																																																																																																									
3	8.30																																																																																																																																											
4	10.30																																																																																																																																											
5	12.30																																																																																																																																											
6	14.30																																																																																																																																											
7	16.30																																																																																																																																											
8	18.30	32	14.20±0.10	28.40																																																																																																																																								
9	20.30																																																																																																																																											
10	22.30																																																																																																																																											
11	24.30																																																																																																																																											
12	26.30	44	20.20±0.10	40.40																																																																																																																																								
13	28.30																																																																																																																																											
14	30.30																																																																																																																																											
15	32.30																																																																																																																																											
16	34.30																																																																																																																																											
17	36.30																																																																																																																																											
18	38.30	56	26.20±0.10	52.40																																																																																																																																								
19	40.30																																																																																																																																											
20	42.30																																																																																																																																											
4	<table border="1"> <thead> <tr> <th>CKT (2.0mm pitch)</th> <th>W</th> <th>PCS/RELL</th> <th>RELL/CARTON</th> <th>SUM(PCS)</th> </tr> </thead> <tbody> <tr> <td>2</td> <td>16</td> <td>600</td> <td>14</td> <td>8400</td> </tr> <tr> <td>3</td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>4</td> <td>24</td> <td>600</td> <td>10</td> <td>6000</td> </tr> <tr> <td>5</td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>6</td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>7</td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>8</td> <td>32</td> <td>600</td> <td>8</td> <td>4800</td> </tr> <tr> <td>9</td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>10</td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>11</td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>12</td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>13</td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>14</td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>15</td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>16</td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>17</td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>18</td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>19</td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>20</td> <td></td> <td></td> <td></td> <td></td> </tr> </tbody> </table>	CKT (2.0mm pitch)	W	PCS/RELL	RELL/CARTON	SUM(PCS)	2	16	600	14	8400	3					4	24	600	10	6000	5					6					7					8	32	600	8	4800	9					10					11					12					13					14					15					16					17					18					19					20									<table border="1"> <thead> <tr> <th>GENERAL TOLERANCE</th> <th colspan="5">DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD</th> </tr> </thead> <tbody> <tr> <td>DIM. TOL. x: ±0.50 x.x: ±0.25 x.xx: ±0.15 GENERAL ANGLE: x: ±2°</td> <td colspan="5">TITLE: PH2.0弯针WTB载带</td> </tr> <tr> <td></td> <td colspan="4">DWG. NO.: WF-PH2.0-XPB1</td> <td>CHECKED: MAX</td> </tr> <tr> <td></td> <td colspan="4">PART NO.: WF-PH2.0-XPB1</td> <td>DRAWN: ELLA</td> </tr> <tr> <td>UNIT: mm</td> <td>SCALE: none</td> <td>SHEET: 1 of 1</td> <td>DWG. SIZE: A4</td> <td>LAYER: bxconn</td> <td>APPROVED: WILL</td> </tr> </tbody> </table>	GENERAL TOLERANCE	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					DIM. TOL. x: ±0.50 x.x: ±0.25 x.xx: ±0.15 GENERAL ANGLE: x: ±2°	TITLE: PH2.0弯针WTB载带						DWG. NO.: WF-PH2.0-XPB1				CHECKED: MAX		PART NO.: WF-PH2.0-XPB1				DRAWN: ELLA	UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL				
CKT (2.0mm pitch)	W	PCS/RELL	RELL/CARTON	SUM(PCS)																																																																																																																																								
2	16	600	14	8400																																																																																																																																								
3																																																																																																																																												
4	24	600	10	6000																																																																																																																																								
5																																																																																																																																												
6																																																																																																																																												
7																																																																																																																																												
8	32	600	8	4800																																																																																																																																								
9																																																																																																																																												
10																																																																																																																																												
11																																																																																																																																												
12																																																																																																																																												
13																																																																																																																																												
14																																																																																																																																												
15																																																																																																																																												
16																																																																																																																																												
17																																																																																																																																												
18																																																																																																																																												
19																																																																																																																																												
20																																																																																																																																												
GENERAL TOLERANCE	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD																																																																																																																																											
DIM. TOL. x: ±0.50 x.x: ±0.25 x.xx: ±0.15 GENERAL ANGLE: x: ±2°	TITLE: PH2.0弯针WTB载带																																																																																																																																											
	DWG. NO.: WF-PH2.0-XPB1				CHECKED: MAX																																																																																																																																							
	PART NO.: WF-PH2.0-XPB1				DRAWN: ELLA																																																																																																																																							
UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL																																																																																																																																							
5																																																																																																																																												

