





4 RECOMMENDED PATTERN

Technical drawing of a recommended pattern for a 2D mold. The drawing shows a rectangular pattern with dimensions and tolerances:

- Overall width: $F \pm 0.1$
- Overall height: 5.3 ± 0.1
- Top edge dimensions: 2 ± 0.1 (width of the top edge) and 2.6 ± 0.1 (height of the top edge).
- Bottom edge dimensions: 2 ± 0.1 (width of the bottom edge) and 1.8 ± 0.1 (height of the bottom edge).
- Internal dimensions: 0.7 ± 0.05 (width of the internal cavity), $P = 1.25 \pm 0.05$ (pitch of the internal cavity), $B \pm 0.05$ (width of the internal cavity), and $E \pm 0.08$ (height of the internal cavity).
- Surface finish: 0.1 ± 0.1 (indicated by a circular feature on the right side).

NOTE 1. LEAD CO-PLANALITY INCLUDE REINFORCED METAL FITTINGS SHALL BE 0.1 MAX.
 ② WHEN THIS CONNECTOR MATES WITH DF14-*S-1.25C , THE MATTING LENGTH IS 7.3mm
 ③ FOR CONNECTORS , 2 OR 3 CONTACTS , SIMPLIFIED LOCK HOLE SHALL BE SET AT THE CENTER OF HOUSING.
 ④ RECOMMENDED METAL MASK THICKNESS:0.15mm
 OPEN AREA RETIO:100%

[illegible]

Nov.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

