












适用线路板(PCB Layout)

Part No	CKT	A	B	C	D
BX-PA2.0-2PWT-BD	2	2.00	4.55	7.95	6.10
BX-PA2.0-3PWT-BD	3	4.00	6.55	9.95	8.10
BX-PA2.0-4PWT-BD	4	6.00	8.55	11.95	10.10
BX-PA2.0-5PWT-BD	5	8.00	10.55	13.95	12.10
BX-PA2.0-6PWT-BD	6	10.00	12.55	15.95	14.10
BX-PA2.0-7PWT-BD	7	12.00	14.55	17.95	16.10
BX-PA2.0-8PWT-BD	8	14.00	16.55	19.95	18.10
BX-PA2.0-9PWT-BD	9	16.00	18.55	21.95	20.10
BX-PA2.0-10PWT-BD	10	18.00	20.55	23.95	22.10
BX-PA2.0-11PWT-BD	11	20.00	22.55	25.95	24.10
BX-PA2.0-12PWT-BD	12	22.00	24.55	27.95	26.10
BX-PA2.0-13PWT-BD	13	24.00	26.55	29.95	28.10
BX-PA2.0-14PWT-BD	14	26.00	28.55	31.95	30.10
BX-PA2.0-15PWT-BD	15	28.00	30.55	33.95	32.10
BX-PA2.0-16PWT-BD	16	30.00	32.55	35.95	34.10

技术指标(Technical Index):

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。

(The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena)

2. 工作温度(Temperature range): -25°C~+85°C.

3. 额定电压(Rated voltage): 250V, AC/DC.

4. 额定电流: 3.0A, AC/DC.

5. 接触电阻(Contact resistance): ≤20mΩ.

6. 绝缘电阻(Insulation resistance): ≥1000MΩ.

7. 耐电压(Withstanding Voltage): 800V AC/minute.

序号	品名	材质	制图	变更内容	日期	GENERAL TOLERANCE	制图	EMMA	料号	BX-PA2.0-NPWT-BD	版本	A
①	2.0 R型卧式WTB嵌芯 2.0 Pitch R/A Wire To Board Housing(H=5.7)	PA6T UL94V-0 米黄色 LCP UL94V-0 米色	DRAWN	DESCRIPTION	DATE	X.±0.50 ±1°	DRAWING	EVA	PART NO.	2.00 Pitch R型卧式WTB	REV.	1/1
②	2.0 R型卧式WTB端子 2.0 Pitch S/T Wire To Board Terminal(H=8.7)	铜合金/表面镀锡 Copper Alloy/ Tin Plating				.X±0.20	审核	JADE	TITLE		SHEET	
③	2.0 R型卧式WTB焊片 2.0 Pitch R/A Wire To Board Fitting Nail(H=5.7)	铜合金/表面镀锡 Copper Alloy/ Tin Plating				.XX±0.10	批准		CUTM.NO.			
							单位	MM	比例	SCALE	1:1	