


1.Features

- Protection for the Following IEC Standards:
 - IEC 61000-4-2 Level 4 ESD Protection
 - These Devices are Pb-Free and are RoHS Compliant
- Low Clamping Voltage
- Stand-Off Voltage: 5 V
- Low Leakage

2.Applications

- High Speed Communication Line Protection
 - • USB 1.1 and 2.0 Power and Data Line Protection
- Digital Video Interface (DVI)
- Monitors and Flat Panel Displays

3.Pinning information



SOT23-6



4. Absolute Maximum Ratings $T_J = 25^\circ\text{C}$


Parameter	Symbol	Maximum	Units
Peak Power Dissipation 8 x 20 μs @ $T_A = 25^\circ\text{C}$ (Note 1)	P_{PK}	500	W
Junction Temperature Range	T_J	-40 to 125	$^\circ\text{C}$
Storage Temperature Range	T_{STG}	-55 to 150	$^\circ\text{C}$
Lead Solder Temperature – Maximum (10 Seconds)	T_L	235	$^\circ\text{C}$
Human Body Model (HBM)	E_{SD}	16000	V
Machine Model (MM)		400	V
IEC 61000-4-2 Air (ESD)		20000	V
IEC 61000-4-2 Contact (ESD)		20000	V
IEC 61000-4-4 (5/50 ns)	EFT	40	A



5. Electrical Characteristic ($T_A=25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Reverse Working Voltage	V_{RWM}	(Note 2)			5	V
Breakdown Voltage	V_{BR}	$I_T=1\text{mA}$, (Note 3)	6			V
Reverse Leakage Current	I_R	$V_{RWM}=5\text{V}$			5	μA
Clamping Voltage	V_C	$I_{PP}=5\text{A}$ (Note 4)			12.5	V
Clamping Voltage	V_C	$I_{PP}=8\text{A}$ (Note 4)			20	V
Maximum Peak Pulse Current	I_{PP}	8x20 μs Waveform (Note 4)			25	A
Junction Capacitance	C_J	$V_R=0\text{V}$, $f=1\text{MHz}$, I/O Pins and GND		3	5	pF
Junction Capacitance	C_J	$V_R=0\text{V}$, $f=1\text{MHz}$, between I/O Pins		1.5	3	pF
Clamping Voltage	V_C	Per IEC 61000-4-2 (Note 6)	Figure 1 and 2			V

6. Electrical Parameters ($T_A=25^\circ\text{C}$ unless otherwise noted)



Uni-Directional TVS

Symbol	Parameter
I_{PP}	Maximum Reverse Peak Pulse Current
V_C	Clamping Voltage @ I_{PP}
V_{RWM}	Working Peak Reverse Voltage
I_R	Maximum Reverse Leakage Current @ V_{RWM}
V_{BR}	Breakdown Voltage @ I_T
I_T	Test Current
I_F	Forward Current
V_F	Forward Voltage @ I_F
P_{PK}	Peak Power Dissipation
C	Capacitance @ $V_R=0$ and $f=1\text{MHz}$



Notes:

2. TVS devices are normally selected according to the working peak reverse voltage (VRWM), which should be equal or greater than the DC or continuous peak operating voltage level.
3. VBR is measured at pulse test current IT.
4. Non-repetitive current pulse per Figure 5 (Pin 5 to Pin 2)
5. Surge current waveform per Figure 5.



6.1Typical characteristic




Figure 1: ESD Clamping Voltage Screenshot
Positive 8 kV Contact per IEC61000-4-2






Figure 2: ESD Clamping Voltage Screenshot
Negative 8 kV Contact per IEC61000-4-2



Level	Test Voltage (kV)	First Peak Current (A)	Current at 30 ns (A)	Current at 60 ns (A)
1	2	7.5	4	2
2	4	15	8	4
3	6	22.5	12	6
4	8	30	16	8




6.2Typical characteristic






7. Typical Applications





8.SOT-23-6 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	c	D	E1	E	e	e1	L	θ
Min	1.050	0.000	1.050	0.300	0.100	2.820	1.500	2.650	0.950	1.800	0.300	0°
Max	1.250	0.100	1.150	0.500	0.200	3.020	1.700	2.950	BSC	2.000	0.600	8°



9.Ordering information



yww: Batch Code

Order Code	Package	Base QTY	Delivery Mode
UMW NUP2201MR6T1G	SOT23-6	3000	Tape and reel



10.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.