

1		2		3		4		5		6		7		8																												
linear dimension (Tolerances Standard GB/T 14486-2008)									—																																	
A	variable range		over 6	over 10	over 30	over 60	over 100	over 160	over 10	over 100																																
	to 6	to 10	to 30	to 60	to 100	to 160	to 10	to 100	to 10	to 100																																
	tolerance	±0.20	±0.30	±0.50	±0.70	±1.00	±1.30	±1.60	0.10	0.30																																
B											<table><tr><th colspan="2">材质及电镀 MATERIAL</th></tr><tr><td>焊针 Pin header</td><td>铜合金, 镀锡 Copper alloy, Tin plated</td></tr><tr><td>塑件 Housing</td><td>PA66, UL94V-0</td></tr><tr><th colspan="2">电气性能 ELECTRICAL</th></tr><tr><td>参考标准 Stanard</td><td>UL IEC</td></tr><tr><td>额定电压 Rated voltage</td><td>300V 320V</td></tr><tr><td>额定电流 Rated current</td><td>10A 15A</td></tr><tr><td>接触电阻 Contact resistance</td><td>20mΩ</td></tr><tr><td>绝缘电阻 Insulation resistance</td><td>500MΩ/DC500V</td></tr><tr><td>耐电压 Withstanding voltage</td><td>AC1600V/1Min</td></tr><tr><th colspan="2">机械性能 MECHANICAL</th></tr><tr><td>温度范围 Temp. range</td><td>-40℃ ~ +105℃</td></tr><tr><td>瞬时温度 Max. soldering</td><td>+250℃ for 5 Sec</td></tr></table>						材质及电镀 MATERIAL		焊针 Pin header	铜合金, 镀锡 Copper alloy, Tin plated	塑件 Housing	PA66, UL94V-0	电气性能 ELECTRICAL		参考标准 Stanard	UL IEC	额定电压 Rated voltage	300V 320V	额定电流 Rated current	10A 15A	接触电阻 Contact resistance	20mΩ	绝缘电阻 Insulation resistance	500MΩ/DC500V	耐电压 Withstanding voltage	AC1600V/1Min	机械性能 MECHANICAL		温度范围 Temp. range	-40℃ ~ +105℃	瞬时温度 Max. soldering	+250℃ for 5 Sec
材质及电镀 MATERIAL																																										
焊针 Pin header	铜合金, 镀锡 Copper alloy, Tin plated																																									
塑件 Housing	PA66, UL94V-0																																									
电气性能 ELECTRICAL																																										
参考标准 Stanard	UL IEC																																									
额定电压 Rated voltage	300V 320V																																									
额定电流 Rated current	10A 15A																																									
接触电阻 Contact resistance	20mΩ																																									
绝缘电阻 Insulation resistance	500MΩ/DC500V																																									
耐电压 Withstanding voltage	AC1600V/1Min																																									
机械性能 MECHANICAL																																										
温度范围 Temp. range	-40℃ ~ +105℃																																									
瞬时温度 Max. soldering	+250℃ for 5 Sec																																									
C																																										
D											编码原则 (Product Number Code): WJ2EDGRC-5.08-XXP-1Y-00A 产品型号 (Series No.) 间距 (Pitch) 极数 (No. of Poles) 客户需求 (Customer Request) 1: 单倍间距 (Single Pitch) 2: 双倍间距 (Double Pitch) 1: 灰色 (Grey) 6: 红色 (Red) 2: 蓝色 (Blue) 7: 透明 (Transparent) 3: 黑色 (Black) 8: 黄色 (Yellow) 4: 绿色 (Green) 9: 白色 (White) 5: 橙色 (Orange)																															
E																																										
F	PCB LAYOUT										<table><tr><th colspan="2">第三视角 (THIRD ANGLE PROJECTION)</th><th colspan="2">插拔式接线端子 PLUG-IN TERMINAL BLOCK</th></tr><tr><td>图纸类型 (TYPE)</td><td>CUSTOMER DRAWING</td><td>型号 (NAME)</td><td>WJ2EDGRC-5.08-XXP-1Y-00A</td></tr><tr><td>单位 (UNITS)</td><td>mm</td><td>版本 (VERSION)</td><td>A</td></tr><tr><td>尺寸 (SIZE)</td><td>A4</td><td colspan="2" rowspan="3"> 宁波康奈克斯电气有限公司 NINGBO KANGNEX ELECTRIC., LTD.</td></tr><tr><td>比例 (SCALE)</td><td>1:1</td></tr><tr><td>图页 (SHEET)</td><td>1/1</td></tr></table>						第三视角 (THIRD ANGLE PROJECTION)		插拔式接线端子 PLUG-IN TERMINAL BLOCK		图纸类型 (TYPE)	CUSTOMER DRAWING	型号 (NAME)	WJ2EDGRC-5.08-XXP-1Y-00A	单位 (UNITS)	mm	版本 (VERSION)	A	尺寸 (SIZE)	A4	宁波康奈克斯电气有限公司 NINGBO KANGNEX ELECTRIC., LTD.		比例 (SCALE)	1:1	图页 (SHEET)	1/1						
第三视角 (THIRD ANGLE PROJECTION)		插拔式接线端子 PLUG-IN TERMINAL BLOCK																																								
图纸类型 (TYPE)	CUSTOMER DRAWING	型号 (NAME)	WJ2EDGRC-5.08-XXP-1Y-00A																																							
单位 (UNITS)	mm	版本 (VERSION)	A																																							
尺寸 (SIZE)	A4	宁波康奈克斯电气有限公司 NINGBO KANGNEX ELECTRIC., LTD.																																								
比例 (SCALE)	1:1																																									
图页 (SHEET)	1/1																																									
G																																										
H																																										
1		2		3		4		5		6		7		8																												