

### Features

- Ultra low leakage: nA level
- Operating voltage: 24V
- Low clamping voltage
- Complies with following standards:
  - IEC 61000-4-2 (ESD) immunity test
    - Air discharge:  $\pm 30\text{kV}$
    - Contact discharge:  $\pm 25\text{kV}$
  - IEC61000-4-4 (EFT) 40A (5/50ns)
  - IEC61000-4-5 (Lightning) 5A (8/20 $\mu\text{s}$ )
- RoHS Compliant

### Applications

- Cell Phone Handsets and Accessories
- Microprocessor based equipment
- Personal Digital Assistants (PDA's)
- Notebooks, Desktops, and Servers
- Portable Instrumentation
- Networking and Telecom
- Serial and Parallel Ports
- Peripherals


### Mechanical Characteristics

- Package: SOD-523
- Lead Finish: Lead Free
- UL Flammability Classification Rating 94V-0
- Quantity Per Reel: 3,000 pcs
- Reel Size: 7 inch
- Device Marking: N5

### Dimensions SOD-523



### Pin Configuration



### Absolute Maximum Ratings (T<sub>amb</sub>=25°C unless otherwise specified)


| Parameter                              | Symbol           | Value       | Unit |
|----------------------------------------|------------------|-------------|------|
| Peak Pulse Power (8/20 $\mu\text{s}$ ) | P <sub>pp</sub>  | 250         | W    |
| ESD per IEC 61000-4-2 (Air)            | V <sub>ESD</sub> | $\pm 30$    | kV   |
| ESD per IEC 61000-4-2 (Contact)        |                  | $\pm 25$    |      |
| Operating Temperature Range            | T <sub>J</sub>   | -55 to +125 | °C   |
| Storage Temperature Range              | T <sub>STJ</sub> | -55 to +150 | °C   |

## Electrical Characteristics


(TA=25°C unless otherwise specified)

| Parameter               | Symbol    | Test Condition                                    | Min  | Typ | Max | Unit          |
|-------------------------|-----------|---------------------------------------------------|------|-----|-----|---------------|
| Reverse Working Voltage | $V_{RWM}$ |                                                   |      |     | 24  | V             |
| Breakdown Voltage       | $V_{BR}$  | $I_T = 1\text{mA}$                                | 25.5 |     |     | V             |
| Reverse Leakage Current | $I_R$     | $V_{RWM} = 24\text{V}$                            |      |     | 1   | $\mu\text{A}$ |
| Clamping Voltage        | $V_C$     | $I_{PP} = 1\text{A}$ (8 x 20 $\mu\text{s}$ pulse) |      |     | 38  | V             |
| Clamping Voltage        | $V_C$     | $I_{PP} = 5\text{A}$ (8 x 20 $\mu\text{s}$ pulse) |      |     | 51  | V             |
| Junction Capacitance    | $C_J$     | $V_R = 0\text{V}$ , $f = 1\text{MHz}$             |      | 27  |     | pF            |


## Typical Performance Characteristics(TA=25°C unless otherwise specified)




Junction Capacitance vs. Reverse Voltage




Clamping Voltage vs. Peak Pulse Current




Peak Pulse Power vs. Pulse Time



IEC61000-4-2 Pulse Waveform




Power Derating Curve




8 X 20us Pulse Waveform

## SOD-523 Package Outline Drawing



| DIMENSIONS       |        |      |      |      |      |
|------------------|--------|------|------|------|------|
| DIM <sup>N</sup> | INCHES |      | MM   |      | NOTE |
|                  | . MIN  | MAX  | MIN  | MAX  |      |
| A                | .043   | .051 | 1.10 | 1.30 | —    |
| B                | .028   | .035 | 0.70 | 0.90 | —    |
| C                | .059   | .067 | 1.50 | 1.70 | —    |
| D                | .020   | .028 | 0.50 | 0.70 | —    |
| E                | .010   | .014 | 0.25 | 0.35 | —    |
| F                | .004   | .008 | 0.10 | 0.20 | —    |
| G                | .020   | .028 | 0.50 | 0.70 | —    |

## Suggested Land Pattern



| DIMENSIONS       |        |      |     |      |      |
|------------------|--------|------|-----|------|------|
| DIM <sup>N</sup> | INCHES |      | MM  |      | NOTE |
|                  | MIN    | MAX  | MIN | MAX  |      |
| C                | —      | .067 | —   | 1.70 | REF  |
| G                | —      | .043 | —   | 1.10 | —    |
| X                | —      | .031 | —   | 0.80 | REF  |
| Y                | —      | .024 | —   | 0.60 | —    |
| Z                | —      | .091 | —   | 2.30 | —    |

### NOTICE

Leiditech reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. Leiditech does not assume any liability arising out of the application or use of any product described herein.