

标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

A

B

C

D

E

F

G

A

B



C

D

E


F

G




SPECIFICATIONS


- 1.Current Rating:9A AC, DC
- 2.Voltage Rating:600V AC, DC
- 3.Temperatuer Range: -25°C~+85°C
- 4.Contact Resistance:20mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 1500V AC/minute
- 7.Material:Phosphoric bronze Tin-plated
- 8.Applicable Wire Sizes:AWG#20~26#




SEC: A-A



SEC: B-B



SEC: C-C



SEC: D-D

1	端子	铜	镀锡	
序号	品名	材质	电镀/颜色	备注



深圳市虹成电子有限公司

品名 TITLE	端子
料号 PART NO	HC-DZ-5557-4.2

GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1	制图 DRAW		AhYe	
X.±0.25	X.*2°	单 位 UNIT	MM	制 图 DRAW	夏操云		
.X±0.20	.X*1°	张 数 PART NO	1 OF 1	审 核 CHECKED	赵亮亮		
.XX±0.15	.XX*±0.5°	版 本 REV	A	批 准 APPROVE			
.XXX±0.10	.XXX*±0.5°						