








技术指标(Technical Index):

- 1.温度范围(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):250V,AC.
- 3.额定电流(Rated current):3.0A AC,DC.
- 4.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 5.耐压值(Withstanding voltage):1000V AC/minute.
- 6.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.

Part No	CKT	A	B
BX-HA2.54-2PZZ-BD	2	2.5	7.5
BX-HA2.54-3PZZ-BD	3	5.0	10.0
BX-HA2.54-4PZZ-BD	4	7.5	12.5
BX-HA2.54-5PZZ-BD	5	10.0	15.0
BX-HA2.54-6PZZ-BD	6	12.5	17.5
BX-HA2.54-7PZZ-BD	7	15.0	20.0
BX-HA2.54-8PZZ-BD	8	17.5	22.5
BX-HA2.54-9PZZ-BD	9	20.0	25.0
BX-HA2.54-10PZZ-BD	10	22.5	27.5
BX-HA2.54-11PZZ-BD	11	25.0	30.0
BX-HA2.54-12PZZ-BD	12	27.5	32.5
BX-HA2.54-13PZZ-BD	13	30.0	35.0
BX-HA2.54-14PZZ-BD	14	32.5	37.5
BX-HA2.54-15PZZ-BD	15	35.0	40.0
BX-HA2.54-16PZZ-BD	16	37.5	42.5
BX-HA2.54-17PZZ-BD	17	40.0	45.0



序号	品名	材质	制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-HA2.54-NPZZ-BD	版本 REV.	A
						X.±0.50	±1°							
①	HA2.5直针WTB胶芯	LCP UL94V-0 米色 白色				.X±0.20		审核 CHECK	EVA		品名 TITLE	HA2.5直针WTB	页次 SHEET	1/1
②	HA2.5直针WTB端子	铜合金/表面镀锡				.XX±0.10		核准 APPROVAL	JADE		客户料号 CUTM.NO.			
								单位 UNITS	MM	比例 SCALE	1:1			



纸箱型号 Carton Type	小型 Small Size	中型 Medium	标准型 Standard
高度 Hight (CM)	7.5	15	32

CKT (2.5mm pitch)	B0	W	F	S
2	7.80	24	11.50	
3	10.30			
4	12.80			
5	15.30	32	14.20±0.10	28.40
6	17.80			
7	20.30			
8	22.80	44	20.20±0.10	40.40
9	25.30			
10	27.80			
11	30.30			
12	32.80	56	26.2±0.10	52.40
13	35.30			
14	37.80			
15	40.30			
16	42.80			

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-HA2.54-NPZZ-BD		版本 REV.	A
			X.±0.50	±1°	审核 CHECK	EVA			品名 TITLE	HA2.5直针WTB		页次 SHEET	1/1
			.X±0.20		核准 APPROVAL	JADE			客户料号 CUTM.NO.				
			.XX±0.10		单位 UNITS	MM	比例 SCALE	1:1	 Bossie (博锡)				