

1.Features

- $V_{DS(V)}=30V$
- $I_D=80A(V_{GS}=10V)$
- $R_{DS(ON)}<1.9m\Omega(V_{GS}=10V)$
- $R_{DS(ON)}<2.2m\Omega(V_{GS}=4.5V)$
- Low Miller Charge
- Low Qrr Body Diode
- UIS Capability (Single Pulse and Repetitive Pulse)


2.Applications

- Starter / Alternator Systems
- Electronic Power Steering Systems
- DC-DC Converters

3.Pinning information

Pin	Symbol	Description
1	G	GATE
2	D	DRAIN
3	S	SOURCE

TO-263



4.Absolute Maximum Ratings $T_c=25^{\circ}C$

Parameter	Symbol	Rating	Units
Drain to Source Voltage	V_{DSS}	30	V
Gate to Source Voltage	V_{GS}	± 20	V
Drain Current Continuous ($T_c<165^{\circ}C$, $V_{GS}=10V$)	I_D	80	A
Drain Current Continuous ($T_c<163^{\circ}C$, $V_{GS}=5V$)		80	A
Drain Current Continuous ($T_{amb}=25^{\circ}C$, $V_{GS}=10V$, with $R_{\theta JA}=43^{\circ}C/W$)		34	A
Pulsed		Figure 4	A
Single Pulse Avalanche Energy (Note 1)	E_{AS}	1246	mJ
Power Dissipation	P_D	300	W
Derate above $25^{\circ}C$		2	W/ $^{\circ}C$
Storage Temperature	T_J, T_{STG}	-55 to 175	$^{\circ}C$



5.Thermal Characteristics

Parameter	Symbol	Rating	Units
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	0.5	°C/W
Thermal Resistance, Junction-to-Ambient (Note 2)	$R_{\theta JA}$	62	°C/W
Thermal Resistance, Junction-to-Ambient ,1in ² copper pad area	$R_{\theta JA}$	43	°C/W



6. Electrical Characteristic ($T_J=25^{\circ}\text{C}$ unless otherwise noted)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Drain to Source Breakdown Voltage	BV_{DSS}	$I_D=250\mu\text{A}$, $V_{GS}=0\text{V}$	30			V
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS}=24\text{V}$ $V_{GS}=0\text{V}$			1	μA
		$T_J=150^{\circ}\text{C}$			250	μA
Gate to Source Leakage Current	I_{GSS}	$V_{GS}=\pm 20\text{V}$			± 100	nA
Gate to Source Threshold Voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}$, $I_D=250\mu\text{A}$	1	1.6	3	V
Drain to Source On Resistance	$R_{DS(on)}$	$I_D=80\text{A}$, $V_{GS}=10\text{V}$		1.4	1.9	m Ω
		$I_D=80\text{A}$, $V_{GS}=5\text{V}$		1.5	2.1	m Ω
		$I_D=80\text{A}$, $V_{GS}=4.5\text{V}$		1.6	2.2	m Ω
Input Capacitance	C_{iss}	$V_{DS}=15\text{V}$, $V_{GS}=0\text{V}$, $f=1\text{MHz}$		11400		pF
Output Capacitance	C_{oss}			2140		pF
Reverse Transfer Capacitance	C_{rss}			1260		pF
Gate Resistance	R_g	$V_{GS}=0.5\text{V}$, $f=1\text{MHz}$		1.2		Ω
Total Gate Charge at 10V	$Q_{g(TOT)}$	$V_{GS}=0\text{V}$ to 10V	$V_{DD}=15\text{V}$ $I_D=80\text{A}$ $I_g=1\text{mA}$	204	265	nC
Total Gate Charge at 5V	$Q_{g(5)}$	$V_{GS}=0\text{V}$ to 5V		100	130	nC
Threshold Gate Charge	$Q_{g(TH)}$	$V_{GS}=0\text{V}$ to 1V		10.9	14.2	nC
Gate to Source Gate Charge	Q_{gs}			33		nC
Gate Charge Threshold to Plateau	Q_{gs2}			22		nC
Gate to Drain "Miller" Charge	Q_{gd}			43		nC
Turn-On Time	$t_{(on)}$	$V_{DD}=15\text{V}$, $I_D=80\text{A}$ $V_{GS}=5\text{V}$, $R_{GS}=1.5\Omega$			155	ns
Turn-On Delay Time	$t_{D(on)}$			24		ns
Rise Time	t_r			73		ns
Turn-Off Delay Time	$t_{D(off)}$			54		ns
Fall Time	t_f			38		ns
Turn-Off Time	t_{off}				149	ns



Source to Drain Diode Forward Voltage	V_{SD}	$I_{SD}=75A$		0.8	1.25	V
		$I_{SD}=40A$		0.8	1	V
Reverse Recovery Time	t_{rr}	$I_F=75A, di/dt=100A/\mu s$		59	77	ns
Reverse Recovery Charge	Q_{rr}	$I_F=75A, di/dt=100A/\mu s$		67	87	nC

Notes:

1: Starting $T_J=25^{\circ}C$, $L=0.61mH$, $I_{AS}=64A$, $V_{DD}=30V$, $V_{GS}=10V$.

2: Pulse width=100s.



7.1 Typical characteristic




Figure 1: Normalized Power Dissipation vs Case Temperature




Figure 2: Maximum Continuous Drain Current vs Case Temperature




Figure 3: Normalized Maximum Transient Thermal Impedance




Figure 4: Peak Current Capability







7.2Typical characteristic

Figure 5: Forward Bias Safe Operating Area	Figure 6: Unclamped Inductive Switching Capability
Figure 7: Transfer Characteristics	Figure 8: Saturation Characteristics
Figure 9: Drain to Source On Resistance vs Gate Voltage and Drain Current	Figure 10: Normalized Drain to Source On Resistance vs Junction Temperature




7.3Typical characteristic

 Figure 11: Normalized Gate Threshold Voltage vs Junction Temperature	 Figure 12: Normalized Drain to Source Breakdown Voltage vs Junction Temperature
 Figure 13: Capacitance vs Drain to Source Voltage	 Figure 14: Gate Charge Waveforms for Constant Gate Current



8.TO-263 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	a	B	b1	b2	H	h	h1	h2	h3	h4	L	L1	L2	L3
Min	9.6	7.2	4.3	1.25	2.2	15.2	1.34	10.3	9.1	1.34	2.5	2.2	1.2	0.7	1.2
Max	10.0	7.6	4.7	1.35	2.6	15.8	1.74	10.7	9.3	1.74	2.9	2.6	1.4	0.9	1.4

Symbol	L4	N
Min	0.4	2.4
Max	0.6	2.5



9.Ordering information



yy: Year Code
ww: Week Code

Order Code	Package	Base QTY	Delivery Mode
UMW FDB8832	TO-263	800	Tape and reel



10.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.